



Auxiliary contact 1 NO standard - for Fupact INF32 to 800

49609

! Discontinued on: 12 Feb 2021

EAN Code: 3303430496090

! Discontinued

Main

Range Of Product	INF32 INF100160 INF40	
	INF63 INF200800	
Range	FuPact	
Device Short Name	auxiliary contact	
Product Or Component Type	Auxiliary contact	
Device Application	Connection	
Range Compatibility	FuPact Fupact INF fuse-switch disconnector	
Auxiliary Contacts Type	Standard	
Signal Contacts Composition	1 NO	
[Ith] Conventional Free Air Thermal Current	16 A	

Complementary

Mounting Mode	Left hand side	
Output Contact Breaking	AC-15: 6 A at 24 V AC 50/60 Hz	
Capacity	AC-15: 6 A at 48 V AC 50/60 Hz	
	DC-12: 6 A at 24 V DC	
	AC-15: 2 A at 660/690 V AC 50/60 Hz	
	AC-15: 3 A at 440 V AC 50/60 Hz	
	AC-15: 4 A at 380/415 V AC 50/60 Hz	
	AC-15: 6 A at 110 V AC 50/60 Hz	
	AC-15: 6 A at 220/240 V AC 50/60 Hz	
	AC-15: 6 A at 250 V AC 50/60 Hz	
	DC-12: 0.1 A at 380/415 V DC	
	DC-12: 0.1 A at 440 V DC	
	DC-12: 0.4 A at 220/240 V DC	
	DC-12: 0.4 A at 250 V DC	
	DC-12: 1.1 A at 110 V DC	
	DC-12: 2 A at 48 V DC	
Minimum Load	10 mA at 24 V	

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1

Contractual warranty

Warranty 18 months



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance

⊘	Reach Free Of Svhc	
⊘	Toxic Heavy Metal Free	
⊘	Mercury Free	
⊘	Rohs Exemption Information Yes	
Ø	Pvc Free	

Certifications & Standards

Eu Rohs Directive	Compliant	
	EU RoHS Declaration	
China Rohs Regulation	China RoHS declaration	
	Pro-active China RoHS declaration (out of China RoHS legal scope)	
Environmental Disclosure	Product Environmental Profile	