# **Product datasheet**

Specifications



# Acti9 - comb busbar - 1L+N - 18 mm pitch - 24 modules - 100 A

Local distributor code: 397362532

A9XPH224

EAN Code: 3606480485039

#### Main

Range	Acti9	
Product Or Component Type	Comb busbar	
Mounting Mode	Horizontal	
Accessory / Separate Part Category	Connection accessory	
Lines Description	1L + N	
Length In 18 Mm Modules	24	

### Complementary

Number Of Ways	12 ways N + 1 L	
Poles Configuration For 1 Way	1 x 1P + N 1 x 2P	
Connection Pitch	18 mm	
Connector Type	Tooth	
Distance Between Way	36 mm	
Marking	NL	
Insulation	Insulated	
Device Presentation	Cuttable	
e] Rated Operational Current 100 A at 40 °C		
[Ue] Rated Operational Voltage	415 V AC	
[Ui] Rated Insulation Voltage	ion Voltage 500 V AC conforming to IEC 61439-2	
Mounting Location	Top or bottom on tunnel type terminals Top or bottom on double terminal	
9 Mm Pitches	48	
Width	430 mm	
Colour	White (RAL 9003)	
Range Compatibility	Acti 9 Acti9 iC60 Acti 9 Acti9 iK60 Acti 9 Acti9 iID Acti 9 Acti9 iID K Acti 9 Acti9 iSW Acti 9 Acti9 iSW-NA Multi9 Multi9 C60	

#### **Environment**

Standards

IEC 60947-7-1 IEC 61439-2

Fire Resistance	960 °C ( 30 s ) conforming to IEC 60695-2-1
Pollution Degree	3 conforming to IEC 60947-7-1
Ip Degree Of Protection	IP20 with end-pieces and tooth covers

# **Packing Units**

•	
Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	5.600 cm
Package 1 Width	8.400 cm
Package 1 Length	46.600 cm
Package 1 Weight	166.000 g
Unit Type Of Package 2	BB1
Number Of Units In Package 2	5
Package 2 Height	5.600 cm
Package 2 Width	8.400 cm
Package 2 Length	46.600 cm
Package 2 Weight	934.000 g
Unit Type Of Package 3	S04
Number Of Units In Package 3	55
Package 3 Height	30.000 cm
Package 3 Width	40.000 cm
Package 3 Length	60.000 cm
Package 3 Weight	11.147 kg

### **Contractual warranty**

Warranty

18 months

### Sustainability Screen

**Green Premium<sup>TM</sup> label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

#### Well-being performance

Reach Free Of Svhc

Toxic Heavy Metal Free	
Mercury Free	
Rohs Exemption Information	Yes

### **Certifications & Standards**

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	No need of specific recycling operations