Product datasheet



Acti9 - comb busbar bottom - 3L+N - 18 mm pitch - 16 modules - 80 A



! Discontinued on: 22 Apr 2021

EAN Code: 3606480795282

(!) Discontinued

Main

Range	Acti9	
Product Or Component Type	Comb busbar	
Mounting Mode	Horizontal	
Accessory / Separate Part Category	Connection accessory	
Lines Description	3L + N	
Length In 18 Mm Modules	16	

Complementary

Number Of Ways	Incomer: 1 way N + 3 L Outgoer: 6 ways N + L	
Poles Configuration For 1 Way	Incomer: 1 x 4P Outgoer: 1 x 1P + N	
Connection Pitch	18 mm	
Connector Type	Tooth	
Distance Between Way	Incomer: 72 mm Outgoer: 36 mm	
Marking	Outgoer: N L1 N L2 N L3 Incomer: N L1 L2 L3	
Insulation	Insulated	
Device Presentation	Cuttable	
[le] Rated Operational Current	80 A at 40 °C	
[Ue] Rated Operational Voltage	230 V AC Ph/N 400 V AC Ph/Ph	
[Ui] Rated Insulation Voltage	500 V AC conforming to IEC 61439-1	
[Uimp] Rated Impulse Withstand Voltage	6 kV	
Mounting Location	Bottom on tunnel type terminals	
9 Mm Pitches	32	
Width	288 mm	
Colour	White (RAL 9003)	
Range Compatibility	Acti 9 Acti9 iC60 Acti 9 Acti9 iID	

Environment

Standards	IEC 60947-7-1
	IEC 61439-1
Fire Resistance	960 °C (30 s) conforming to IEC 60695-2-1
Pollution Degree	3 conforming to IEC 60947-7-1
Ip Degree Of Protection	IP20 with end-pieces and tooth covers

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	3 cm
Package 1 Width	2.2 cm
Package 1 Length	28.7 cm
Package 1 Weight	175 g

Contractual warranty

Warranty 18 months



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance

Ø	Reach Free Of Svhc	
②	Toxic Heavy Metal Free	
Ø	Mercury Free	
⊘	Rohs Exemption Information	Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	No need of specific recycling operations