# **Product datasheet**





Pilot light, Harmony 9001K, metal, polycarbonate, fresnel, clear, 30mm, neon, 480V

9001KP14C31

! Discontinued on: 4 Aug 2021

! To be end-of-service on: 15 Aug 2024

# ! Discontinued

#### Main

Range Of Product	Harmony 9001K	
Product Or Component Type	Pilot light	
Device Short Name	9001K	

## Complementary

Metal
30 mm
Round
Domed plastic
Clear
neon
BA 9s
Direct 480 V AC/DC
Screw clamp terminals, 1 x 0.222 x 1.5 mm² conforming to IEC 60947-1
0.8 N.m conforming to IEC 60947-1
Cross slotted
Any position
250 V (pollution degree 2) conforming to IEC 60947-1
2.5 kV conforming to IEC 60947-1
10 A cartridge fuse conforming to IEC 60947-5-1
Neon
10 A
54 mm
70 mm
42 mm
0.21 kg
Fresnel
480 V
Polycarbonate

Life Is On Schneider 19 Apr 2024



Size 30 mm

### **Environment**

Standards	EN/IEC 60947-5-4
	EN/IEC 60947-1
	JIS C8201-5-1
	CSA C22.2 No 14
	EN/IEC 60947-5-1
	UL 508
	JIS C 852
	JIS C8201-1
Product Certifications	NEMA
	UL 508
Protective Treatment	TC
Ambient Air Temperature For Storage	-4070 °C
Ambient Air Temperature For Operation	-2570 °C
Vibration Resistance	7 gn (f= 2500 Hz) conforming to IEC 60068-2-6
Shock Resistance	50 gn conforming to IEC 60068-2-27
Overvoltage Category	Class II conforming to IEC 61140
Ip Degree Of Protection	IP66 conforming to IEC 60529
Nema Degree Of Protection	NEMA 1
	NEMA 12
	NEMA 13
	NEMA 2
	NEMA 3
	NEMA 3R
	NEMA 4
	NEMA 6
	TILITU I V

# **Packing Units**

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	12.903 cm
Package 1 Width	5.08 cm
Package 1 Length	32.774 cm
Package 1 Weight	226.796 g

## **Contractual warranty**

Warranty 18 months



**Green Premium**<sup>TM</sup> **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

#### Well-being performance



Mercury Free



Rohs Exemption Information

Yes

#### **Certifications & Standards**

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
China Rohs Regulation	China RoHS declaration
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	No need of specific recycling operations