Product datasheet

Specifications





Acti9 - MINs - silent electronic timer - adjustable from 0.5 to 20 minutes

Local distributor code: 391537554

CCT15232

EAN Code: 3303431062621

Main

mann	
Range Of Product	Acti9
Product Name	Acti9 MIN
Device Short Name	MINs
Product Or Component Type	Silent electronic timer
Product Compatibility	Mechanical compatibility with electrical comb busbars
Colour Tint	White (RAL 9003)

Complementary

Device Application	Building
Load Type	230 V AC halogen lamp 2300 W 230 V AC incandescent lamp 2300 W Fluorescent lamp 9 x electronic ballast 7 W Dual mounted fluorescent tubeconventional ballast 2300 VA Fluorescent tubeelectronic ballast 300 VA Non-corrected fluorescent tubeconventional ballast 2300 VA Serial-corrected fluorescent tubeconventional ballast 2300 VA Fluorescent lamp 7 x electronic ballast 11 W Fluorescent lamp 7 x electronic ballast 15 W Fluorescent lamp 7 x electronic ballast 20 W Fluorescent lamp 7 x electronic ballast 23 W Fluorescent lamp 7 x electronic ballast 23 W Fluorescent lamp 7 x electronic ballast 1500 VA
Power Consumption In Va	6 VA
Maximum Switching Current	16 A - 230 V AC pf = 1
[Ue] Rated Operational Voltage	230 V AC +10 % -15 % at 50/60 Hz
Time Delay	Adjustable from 0.5 to 20 minutes
Mounting Support	DIN rail
9 Mm Pitches	2
Connections - Terminals	Screw terminals - <= 6 mm ²
Electrical Insulation Class	Class II
Width	18 mm
Height	89 mm
Depth	66 mm
Net Weight	75 g

Environment

Ambient Air Temperature For -10...50 °C Operation

Ip Degree Of Protection	IP20 B
ip Bogioo et i totootion	11 20 0

Packing Units

r acking onits	
Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	7.0 cm
Package 1 Width	7.0 cm
Package 1 Length	10.0 cm
Package 1 Weight	93.0 g
Unit Type Of Package 2	\$03
Number Of Units In Package 2	130
Package 2 Height	30.0 cm
Package 2 Width	30.0 cm
Package 2 Length	40.0 cm
Package 2 Weight	12.636 kg

Contractual warranty

Warranty

18 months

Sustainability Screen

Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

Well-being performance

Mercury Free

Rohs Exemption Information Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End of Life Information