



# Lisse - 2-pole key switch module - 20AX - white

Local distributor code: 400146153

0146153 GGBL20DPKWPW

EAN Code: 3606480642463

#### Main

Range	Lisse
Aesthetic Name	White moulded
Product Or Component Type	Switch module
Device Presentation	Flush-mounting module
Colour Tint	White
Quantity Per Set	Set of 1

## Complementary

Switch Function	2-pole
Control Type	Key switch
Device Mounting	Wall mounted
Rated Current	20 AX
Connections - Terminals	Screw terminals
Material	Urea (carbamide)
Surface Finish	Matt
Type Of Packing	Carton
Height	59 mm
Width	25 mm
Depth	24 mm
Net Weight	0.021 kg

## **Environment**

Standards	BS EN 60669-1
Ip Degree Of Protection	IP20

## **Packing Units**

25 Apr 2024

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	2 cm
Package 1 Width	2.4 cm
Package 1 Length	5.9 cm
Package 1 Weight	26.3 g

Unit Type Of Package 2	BB1
Number Of Units In Package 2	6
Package 2 Height	6.8 cm
Package 2 Width	6.5 cm
Package 2 Length	8.5 cm
Package 2 Weight	178.7 g
Unit Type Of Package 3	CAR
Number Of Units In Package 3	600
Package 3 Height	15.5 cm
Package 3 Width	44.5 cm
Package 3 Length	68 cm
Package 3 Weight	18.538 kg

## **Contractual warranty**

Warranty 18 months



**Green Premium**<sup>TM</sup> **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



RoHS/REACh

## Well-being performance

<b>②</b>	Toxic Heavy Metal Free	
<b>⊘</b>	Mercury Free	
<b>⊘</b>	Rohs Exemption Information	Yes

#### **Certifications & Standards**

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant
	EU RoHS Declaration
China Rohs Regulation	China RoHS declaration
	Pro-active China RoHS declaration (out of China RoHS legal scope)
Circularity Profile	End of Life Information