



Linergy FT - Comb busbar - 63 A -4 tap-offs - 54 mm pitch

Local distributor code:

23052158

GV2G454

EAN Code: 3389110555875

Main

Range	Linergy	
Product Name	FT	
Device Short Name	GV2G	
Product Or Component Type	Comb busbar	
Accessory / Separate Part Category	Connection accessory	
Poles Description	3P	
Range Compatibility	TeSys Deca TeSys GV2 TeSys K TeSys U	
Number Of Tap-Offs	4	
[Ith] Conventional Free Air Thermal Current	63 A	
Connection Pitch	54 mm	

Complementary

Mounting Location	On terminal
[Ui] Rated Insulation Voltage	690 V
Length	206 mm
Net Weight	0.085 kg

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	1.900 cm
Package 1 Width	3.700 cm
Package 1 Length	21.600 cm
Package 1 Weight	88.000 g
Unit Type Of Package 2	S01
Number Of Units In Package 2	50
Package 2 Height	15.000 cm
Package 2 Width	15.000 cm
Package 2 Length	40.000 cm
Package 2 Weight	4.628 kg

Unit Type Of Package 3	P06
Number Of Units In Package 3	1600
Package 3 Height	75.000 cm
Package 3 Width	60.000 cm
Package 3 Length	80.000 cm
Package 3 Weight	156.500 kg

Contractual warranty

Warranty 18 months



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance


⊘	Reach Free Of Svhc	
Ø	Toxic Heavy Metal Free	
⊘	Mercury Free	
⊘	Rohs Exemption Information	Yes

Certifications & Standards

Reach Regulation	REACh Declaration	
Eu Rohs Directive	Compliant EU RoHS Declaration	
China Rohs Regulation	China RoHS declaration	
Environmental Disclosure	Product Environmental Profile	
Circularity Profile	End of Life Information	

Dimensions Drawings

Sets of Busbars GV2G445, GV2G454, GV2G472, with Terminal Block GV2G05



	1	р
GV2G445 (4 x 45 mm)	179	45
GV2G454 (4 x 54 mm)	206	54
GV2G472 (4 x 72 mm)	260	72

Number of ten offe	а			
Number of tap-offs	5	6	7	8
GV2G445	224	269	314	359
GV2G454	260	314	368	422
GV2G472	332	404	476	548