

Product datasheet

Specifications



Linergy FT - Comb busbar - 63 A - 4 tap-offs - 72 mm pitch



Local distributor code:
23052161

GV2G472

EAN Code: 3389110555868

Main

Range	Linergy
Product Name	FT
Device Short Name	GV2G
Product Or Component Type	Comb busbar
Accessory / Separate Part Category	Connection accessory
Poles Description	3P
Range Compatibility	TeSys D TeSys GV2 TeSys K TeSys U
Number Of Tap-Offs	4
[Ith] Conventional Free Air Thermal Current	63 A
Connection Pitch	72 mm

Complementary

Mounting Location	On terminal
[U] Rated Insulation Voltage	690 V
Length	260 mm
Net Weight	0.094 kg

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	1.2 cm
Package 1 Width	3.2 cm
Package 1 Length	26 cm
Package 1 Weight	110 g
Unit Type Of Package 2	S01
Number Of Units In Package 2	40
Package 2 Height	15 cm
Package 2 Width	15 cm
Package 2 Length	40 cm
Package 2 Weight	4.502 kg

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability

Green Premium™ label is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)



Transparency RoHS/REACH

Well-being performance


✓	Reach Free Of Svhc	
✓	Toxic Heavy Metal Free	
✓	Mercury Free	
✓	Rohs Exemption Information	Yes

Certifications & Standards

Reach Regulation	REACH Declaration
Eu Rohs Directive	Compliant EU RoHS Declaration
China Rohs Regulation	China RoHS declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End of Life Information

Dimensions Drawings

Sets of Busbars GV2G445, GV2G454, GV2G472, with Terminal Block GV2G05



	l	p
GV2G445 (4 x 45 mm)	179	45
GV2G454 (4 x 54 mm)	206	54
GV2G472 (4 x 72 mm)	260	72

Number of tap-offs	a			
	5	6	7	8
GV2G445	224	269	314	359
GV2G454	260	314	368	422
GV2G472	332	404	476	548