

Product datasheet

Specifications



ULT.SCRWLS Flat Plate-1Gang-13A-DP-switched with neon-Polished brass

Local distributor code:
400084147

GU3411DBPB

⚠ Discontinued on: 18 Oct 2020

⚠ To be discontinued

EAN Code: 5018486552147

Main

Aesthetic Name	Screwless flat plate
Product Or Component Type	Switched socket
Rated Current	13 A at 230 V AC 50 Hz
Fixing Mode	By screws M3.5 x 30 mm
Colour Tint	Polished brass

Complementary

Device Presentation	Complete product
Outlet Poles Configuration	2P
Outlet Standard Description	3 pins
Outlet Standard Deviation	British
Actuator	Rocker
Number Of Gangs	1 gang
Earth Circuit	Standard earth
Pilot Light	Neon indicator
Device Mounting	Wall mounted
Connections - Terminals	Screw terminal
Material	Steel
Quantity Per Set	Set of 1
Height	88 mm
Width	148 mm
Depth	30 mm
Socket Number	2

Environment

Ip Degree Of Protection	IP20
Standards	BS 1363

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Package 1 Height	4.000 cm
Package 1 Width	9.500 cm
Package 1 Length	9.700 cm
Package 1 Weight	214.500 g
Unit Type Of Package 2	CAR
Number Of Units In Package 2	100
Package 2 Height	21.500 cm
Package 2 Width	42.000 cm
Package 2 Length	50.000 cm
Package 2 Weight	22.011 kg
Unit Type Of Package 3	PAM
Number Of Units In Package 3	1600
Package 3 Height	102.500 cm
Package 3 Width	120.000 cm
Package 3 Length	100.000 cm
Package 3 Weight	372.181 kg

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability


Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)

Well-being performance

 Rohs Exemption Information	Yes
Reach Regulation	REACH Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration