Product datasheet

Specifications





TeSys D - suppressor module - varistor - 50...127 V AC

Local distributor code: 381818212

LAD4VG

EAN Code: 3389110385618

Main

Range	TeSys	
Device Short Name	LAD4	
Product Or Component Type	Suppressor module	
Product Compatibility	3P LC1D09D38 4P LC1DT20DT40 4P LC1D098D258 CAD32, CAD50	

Complementary

Mounting Location	Front Front Front Front Front Front Front Front Front Front Front Front Front Front	
Mounting Mode	By clips	
Suppressor Technology	Varistor (peak limiting)	
[Uc] Control Circuit Voltage	50127 V AC	
Maximum Peak Voltage	2 Uc	
Net Weight	0.012 kg	

Environment

Standards	IEC 60947-5-1 EN 60947-5-1 CSA C22.2 No 60947-5-1 UL 60947-5-1 GB/T 14048.5
Product Certifications	UL CSA
Ip Degree Of Protection	IP2X conforming to IEC 60529
Ambient Air Temperature For Operation	-2555 °C
Ambient Air Temperature For Storage	-4080 °C

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	1.100 cm
Package 1 Width	10.000 cm
Package 1 Length	5.000 cm
Package 1 Weight	12.000 g
Unit Type Of Package 2	S01
Number Of Units In Package 2	70
Package 2 Height	15.000 cm
Package 2 Width	15.000 cm
Package 2 Length	40.000 cm
Package 2 Weight	1.180 kg
Unit Type Of Package 3	P06
Number Of Units In Package 3	1120
Package 3 Height	45.000 cm
Package 3 Width	60.000 cm
Package 3 Length	80.000 cm
Package 3 Weight	25.540 kg

Contractual warranty

Warranty

18 months

Sustainability Screen Premium

Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

Well-being performance

Reach Free Of Svhc
Toxic Heavy Metal Free
Mercury Free
Rohs Exemption Information Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant
	EU RoHS Declaration
China Rohs Regulation	China RoHS declaration
	Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	No need of specific recycling operations