
Product datasheet

Specification





CENTRE FEED BOX 250 A

Local distributor code:

2222051 KSA250ABT4

EAN Code: 3606480004032

Main

| Range Of Product | Canalis |
|--------------------------------|--------------------------------------|
| Product Name | KS |
| Device Short Name | KSA |
| Product Compatibility | Canalis KSA busbar trunking 100250 A |
| Offer Type | Classic |
| Product Or Component Type | Feed unit |
| Conductors Material | Aluminium |
| [le] Rated Operational Current | 250 A |
| [Ue] Rated Operational Voltage | 230690 V |
| Number Of Circuits | 1 |
| Busbar Trunking Polarity | 3L + N + PE |
| Protection Type | Without protection |
| Control Type | Without |
| Colour | White (RAL 9001) |

Complementary

| Provided Equipment | End cover |
|-------------------------|---|
| Mounting Location | Central |
| Mounting Mode | By screws |
| Mounting Support | Busbar |
| Body Material | Metal |
| Connections - Terminals | Lug for 240 mm² flexible Lug for 240 mm² rigid |
| Width | 585 mm |
| Depth | 173.5 mm |
| Height | 436 mm |
| Net Weight | 13 kg |
| Standards | IEC 61439-1 IEC 61439-6 |

Environment

Ip Degree Of Protection IP55 conforming to IEC 60529

Ik Degree Of Protection IK08 conforming to IEC 62262

Packing Units

| Unit Type Of Package 1 | PCE |
|------------------------------|-----------|
| Number Of Units In Package 1 | 1 |
| Package 1 Height | 20.500 cm |
| Package 1 Width | 48.000 cm |
| Package 1 Length | 63.300 cm |
| Package 1 Weight | 13.700 kg |
| Unit Type Of Package 2 | P06 |
| Number Of Units In Package 2 | 5 |
| Package 2 Height | 82.000 cm |
| Package 2 Width | 80.000 cm |
| Package 2 Length | 60.000 cm |
| Package 2 Weight | 74.900 kg |

Contractual warranty

Warranty 18 months



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance

| ⊘ | Reach Free Of Svhc |
|----------|--------------------------------|
| ⊘ | Toxic Heavy Metal Free |
| ⊘ | Mercury Free |
| ⊘ | Rohs Exemption Information Yes |
| Ø | Halogen Free Product |

Certifications & Standards

| Reach Regulation | REACh Declaration |
|--------------------------|---|
| Eu Rohs Directive | Compliant EU RoHS Declaration |
| China Rohs Regulation | China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope) |
| Environmental Disclosure | Product Environmental Profile |
| Weee | The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins |
| Circularity Profile | No need of specific recycling operations |