
# **Product datasheet**

Specifications





! Discontinued

Tap off unit, Canalis KS 500A to 1000A, for ComPacT NSX400, with 1 current transformer, 250A, 3L+N+PE, IP55, RAL9001

KSB400DC4TRE

**!** 

! Discontinued on: 23 Jun 2022

EAN Code: 3606485057712

#### Main

Range Of Product	Canalis
Range Compatibility	Canalis KS busbar trunking Canalis KT busbar trunking
Offer Type	Advanced
Product Or Component Type	Tap-off unit
[le] Rated Operational Current	400 A at 35 °C
Protection Type	Circuit breaker: Compact NSX400
Provided Equipment	circuit-breaker to be ordered separately current transformer to be ordered separately
Mounting Mode	Plug-in with fixed polarity
Tap-Off Unit Polarity	3L+N+PE
Colour	White (RAL 9001)

### Complementary

Device Application	Medium power distribution
[Ue] Rated Operational Voltage	400 V depending on protective device 500 V depending on protective device
[Uimp] Rated Impulse Withstand Voltage	6.8 kV
[Ui] Rated Insulation Voltage	400 V depending on protective device 500 V depending on protective device
Network Frequency	50/60 Hz
Control Type	Extended rotary handle
Electrical Connection	Crimp lug - ISO50 240 mm² flexible Crimp lug - ISO50 240 mm² rigid
Door/Cover Opening Side	Right
Tap-Off Unit Disconnection Mode	By opening the door
Number Of Openings	2 openings for FL21 gland plate
Standards	IEC 61439-6 IEC 61439-1
Body Material	Metal
Width	732 mm
Depth	350 mm

Depth (Door Open)	976.5 mm
Height	438 mm
Net Weight	20 kg

### **Environment**

Earthing System	TT TN-S IT
Ip Degree Of Protection	IP55 conforming to IEC 60529
Ik Degree Of Protection	IK08 conforming to IEC 62262

# **Packing Units**

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	35.0 cm
Package 1 Width	44.0 cm
Package 1 Length	73.5 cm
Package 1 Weight	21.0 kg
Unit Type Of Package 2	P12
Number Of Units In Package 2	4
Package 2 Height	95.0 cm
Package 2 Width	80.0 cm
Package 2 Length	120.0 cm
Package 2 Weight	92.0 kg

## **Contractual warranty**

Warranty 18 months



**Green Premium**<sup>TM</sup> **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

### Well-being performance



Mercury Free



Rohs Exemption Information

Yes

#### **Certifications & Standards**

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration  Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	No need of specific recycling operations