Product datasheet

Specification





Module IFE - Modbus TCP - Ethernet IP & MBSL

LV434002

EAN Code: 3606481283146

Main

Range Of Product	ComPact NSX100250
	ComPact NSX400630
	ComPact NS630b1600
	ComPact NS1600b3200
Device Short Name	IFE
Product Or Component Type	Interface module
Range Compatibility	Masterpact MasterPact MTZ
	Masterpact MasterPact NT
	Masterpact MasterPact NW
	ComPact ComPact NSX
	ComPact ComPact NS630b1600
	ComPact ComPact NS1600b3200
	PowerPact PowerPact J
	PowerPact PowerPact L
	PowerPact PowerPact H
	PowerPact PowerPact P
	PowerPact PowerPact R

Complementary

Communication Network Type	Ethernet, Modbus TCP/IP, HTTP, FTP, SMTP, NTP, SNMP10/100 Mbit/s on 2-port
	RJ45
	Universal Logic Plug on 2-port RJ45
	Modbus TCP/IP, Modbus TCP master9.638.4 kbauds
Communication Gateway	Ethernet TCP/IP to Modbus
Web Server	Embedded HTTP server
Mounting Mode	By clips
Mounting Support	35 mm DIN rail
Control Type	By software
[Us] Rated Supply Voltage	24 V DC - 2010 %
Maximum Supply Current	3 A
Current Consumption	120 mA
Connections - Terminals	RJ45 connector
Product Certifications	CE
	GOST
	cULus
	FCC
Standards	IEC 60947-6-2
	UL 508
	UL 60950
	IEC 60950
Height	105 mm
Width	72 mm

Depth	71 mm	
Net Weight	182.5 g	
Accessory / Separate Part Spare part for Compact NS630b1600 Category Spare part for Compact NS1600b3200		

Environment

Ip Degree Of Protection	Connectors: IP2X Other parts: IP3x Front panel: IP4X
Relative Humidity	585 %
Ambient Air Temperature For Storage	-4085 °C
Ambient Air Temperature For Operation	-2070 °C
Pollution Degree	3
Flame Retardance	V0 conforming to UL 94 V0 conforming to IEC 60947-1 V0 conforming to IEC 60695-2-11
Shock Resistance	1000 m/s²
Vibration Frequency	58.4 Hz

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	7.1 cm
Package 1 Width	7.2 cm
Package 1 Length	10.5 cm
Package 1 Weight	188.0 g
Unit Type Of Package 2	P06
Number Of Units In Package 2	192
Package 2 Height	60.0 cm
Package 2 Width	80.0 cm
Package 2 Length	70.0 cm
Package 2 Weight	61.786 kg
Unit Type Of Package 3	S03
Number Of Units In Package 3	24
Package 3 Height	30.0 cm
Package 3 Width	30.0 cm
Package 3 Length	40.0 cm
Package 3 Weight	6.723 kg

Contractual warranty

Warranty 18 months



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance

Mercury Free
Rohs Exemption Information Yes
Pvc Free
Halogen Free Plastic Parts Product

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	End of Life Information