

# Product datasheet

Specifications



## ClimaSys CA - CSVS SmartGrid for cut-out 125x125mm

Local distributor code:  
407698028

NSYCAG125DG

EAN Code: 3606481369840

### Main

Range	ClimaSys
Product	ClimaSys CA
Range Compatibility	ClimaSys ClimaSys CV
Product Or Component Type	Outlet grille
Accessory / Separate Part Category	Thermal management accessory
Type Of Front Cover	Smoked
Accessory / Separate Part Destination	ClimaSys ventilation system
Fixing Mode	By screws Clipped
Device Composition	1 front cover: rear of outlet grille 1 motor support: embedded in filter 1 G2 M1 synthetic standard filter 1 dust sensor
Quantity Per Set	Set of 1

### Complementary

Material	Front cover: injected thermoplastic (PC) Motor support: injected thermoplastic (ASA PC)
Colour	Front cover: smoked black (RAL 9005) Motor support: black (RAL 9005)
Cut-Out Dimensions	125 x 125 mm
Height	170 mm external:
Width	150 mm external:
Depth	15 mm external:
Ip Degree Of Protection	IP54

### Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	4.5 cm
Package 1 Width	16.0 cm
Package 1 Length	18.0 cm
Package 1 Weight	220.0 g
Unit Type Of Package 2	CAR

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Number Of Units In Package 2	20
Package 2 Height	39.5 cm
Package 2 Width	30.0 cm
Package 2 Length	40.0 cm
Package 2 Weight	4.828 kg

## Contractual warranty

Warranty	18 months
----------	-----------

Sustainability



**Green Premium™ label** is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)



Transparency   RoHS/REACH

## Well-being performance

 Mercury Free

 RoHS Exemption Information   [Yes](#)

## Certifications & Standards

Reach Regulation	<a href="#">REACH Declaration</a>
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
China Rohs Regulation	<a href="#">China RoHS declaration</a> Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	No need of specific recycling operations