# **Product datasheet**

Specifications





## D40A to D65A RC 24-48V

Suppressor Local distributor code:

393395613

LAD4RC3E

EAN Code: 3389119410168

#### Main

Range	TeSys TeSys Deca	
Device Short Name	LAD4	
Product Or Component Type	Suppressor module	
Product Compatibility	3P LC1D40AD80A 4P LC1DT60ADT80A	

#### Complementary

Mounting Location	Front	
Mounting Mode	By clips	
Suppressor Technology	RC circuit	
[Uc] Control Circuit Voltage	2448 V AC	
Maximum Peak Voltage	3 Uc	
Net Weight	0.02 kg	
Colour	Dark grey	

#### Environment

Standards	IEC 60947-5-1 EN 60947-5-1 CSA C22.2 No 60947-5-1 UL 60947-5-1 GB/T 14048.5
Product Certifications	UL CSA
Ip Degree Of Protection	IP2X conforming to IEC 60529
Ambient Air Temperature For Operation	-2555 °C
Ambient Air Temperature For Storage	-4080 °C

### **Packing Units**

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	1.500 cm
Package 1 Width	2.000 cm
Package 1 Length	5.000 cm
Package 1 Weight	16.000 g

Unit Type Of Package 2	BB1
Number Of Units In Package 2	10
Package 2 Height	6.300 cm
Package 2 Width	7.300 cm
Package 2 Length	12.200 cm
Package 2 Weight	184.000 g
Unit Type Of Package 3	S01
Number Of Units In Package 3	100
Package 3 Height	15.000 cm
Package 3 Width	15.000 cm
Package 3 Length	40.000 cm
Package 3 Weight	2.063 kg

## **Contractual warranty**

Warranty

18 months

### Sustainability Screen Premium

**Green Premium<sup>TM</sup> label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

#### Well-being performance

Reach Free Of Svhc
Toxic Heavy Metal Free
Mercury Free
Rohs Exemption Information Yes

#### **Certifications & Standards**

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant
	EU RoHS Declaration
China Rohs Regulation	China RoHS declaration
	Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	No need of specific recycling operations