Product datasheet

Specifications





D40A to D65A RC 110-240V Suppressor

Local distributor code: 392951362

LAD4RC3U

EAN Code: 3389119410182

Main

Range	TeSys TeSys Deca
Device Short Name	LAD4
Product Or Component Type	Suppressor module
Product Compatibility	3P LC1D40AD80A 4P LC1DT60ADT80A

Complementary

Mounting Location	Front	
Mounting Mode	By clips	
Suppressor Technology	RC circuit	
[Uc] Control Circuit Voltage	110240 V AC	
Maximum Peak Voltage	3 Uc	
Net Weight	0.04 kg	
Colour	Dark grey	

Environment

Standards	IEC 60947-5-1 EN 60947-5-1 CSA C22.2 No 60947-5-1 UL 60947-5-1 GB/T 14048.5	
Product Certifications	UL CSA	
Ip Degree Of Protection	IP2X conforming to IEC 60529	
Ambient Air Temperature For Operation	-2555 °C	
Ambient Air Temperature For Storage	-4080 °C	

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	1.500 cm
Package 1 Width	5.000 cm
Package 1 Length	8.000 cm
Package 1 Weight	16.000 g

Unit Type Of Package 2	BB1
Number Of Units In Package 2	10
Package 2 Height	6.500 cm
Package 2 Width	7.500 cm
Package 2 Length	12.500 cm
Package 2 Weight	186.000 g
Unit Type Of Package 3	S01
Number Of Units In Package 3	100
Package 3 Height	15.000 cm
Package 3 Width	15.000 cm
Package 3 Length	40.000 cm
Package 3 Weight	2.070 kg

Contractual warranty

Warranty 18 months



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance

Ø	Reach Free Of Svhc	
⊘	Toxic Heavy Metal Free	
Ø	Mercury Free	
⊘	Rohs Exemption Information	Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	No need of specific recycling operations