



# TeSys D - suppressor module - bidirectional peak limiting diode - 73...125 V AC/DC

Local distributor code:
393395655 LAD4T3G

EAN Code: 3389119410267

#### Main

Range	TeSys TeSys Deca
Device Short Name	LAD4
Product Or Component Type	Suppressor module
Product Compatibility	3P LC1D40AD80A 4P LC1DT60ADT80A

# Complementary

Mounting Location	Front	
Mounting Mode	By clips	
Suppressor Technology	Bidirectional peak limiting diode	
[Uc] Control Circuit Voltage	73125 V AC/DC 50/60 Hz	
Maximum Peak Voltage	2 Uc	
Net Weight	0.02 kg	
Colour	Dark grey	

## **Environment**

Standards	IEC 60947-5-1 EN 60947-5-1 CSA C22.2 No 60947-5-1 UL 60947-5-1 GB/T 14048.5
Product Certifications	UL CSA
Ip Degree Of Protection	IP2X conforming to IEC 60529
Ambient Air Temperature For Operation	-2555 °C
Ambient Air Temperature For Storage	-4080 °C

# **Packing Units**

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	2.0 cm
Package 1 Width	7.0 cm
Package 1 Length	2.0 cm
Package 1 Weight	17.0 g

Unit Type Of Package 2	BB1
Number Of Units In Package 2	10
Package 2 Height	6.2 cm
Package 2 Width	7.5 cm
Package 2 Length	12.0 cm
Package 2 Weight	191.0 g
Unit Type Of Package 3	S01
Number Of Units In Package 3	100
Package 3 Height	15.0 cm
Package 3 Width	15.0 cm
Package 3 Length	40.0 cm
Package 3 Weight	2.147 kg

# **Contractual warranty**

Warranty 18 months



**Green Premium**<sup>TM</sup> **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

## Well-being performance

<b>Ø</b>	Reach Free Of Svhc	
<b>⊘</b>	Toxic Heavy Metal Free	
<b>Ø</b>	Mercury Free	
<b>⊘</b>	Rohs Exemption Information	Yes

#### **Certifications & Standards**

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant EU RoHS Declaration
China Rohs Regulation	China RoHS declaration  Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	No need of specific recycling operations