Product datasheet

Specification





wall-mounting enclosure polyester monobloc IP66 H747xW536xD300mm

Local distributor code: 403422816 NSYPLM75G

EAN Code: 3606480776694

Main

Range	Thalassa
Product Name	Thalassa PLM
Device Short Name	PLM
Enclosure Type	Multi-purpose
Category	Compact enclosure
Nominal Height	747 mm
Nominal Width	536 mm
Nominal Depth	300 mm
Enclosure Mounting	Wall mounted
Device Composition	1 body 1 door 2 lock
Door Type	Plain
Lock Type	3 mm double-bar lock

Complementary

Number Of Locks	2
Mounting Plate Description	Without mounting plate
Accessibility For Operation	Front
Removable Parts	Door by hinges
Material	Polyester reinforced with fibreglass
Colour	Grey (RAL 7035)
Standards	IEC 62208 NEMA classification 13 NEMA classification 4X
Product Certifications	UL
Electrical Insulation Class	Class II

Environment

Ip Degree Of Protection	IP66 conforming to IEC 60529
Ik Degree Of Protection	IK10 conforming to IEC 62262
Fire Resistance	960 °C conforming to IEC 62208
Ambient Air Temperature For Operation	-4080 °C

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	32.500 cm
Package 1 Width	55.500 cm
Package 1 Length	80.500 cm
Package 1 Weight	14.781 kg
Unit Type Of Package 2	PAM
Number Of Units In Package 2	12
Package 2 Height	220.000 cm
Package 2 Width	100.000 cm
Package 2 Length	120.000 cm
Package 2 Weight	190.372 kg

Contractual warranty

Warranty 18 months



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance



Mercury Free



Rohs Exemption Information

Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations