Product datasheet

Specifications





TeSys LE - enclosed DOL starter - 25 A - 240 V AC coil

Local distributor code:

381826945 LE1D25U7

EAN Code: 3389110586053

Main

Range	TeSys	
Product Name	TeSys LE	
Device Short Name	LE1D	
Product Or Component Type	Enclosed DOL starter	
Device Application	Standard	
Utilisation Category	AC-3	
Device Composition	Thermal overload relay ordered separately Contactor	
Control Type	Push-button start green I Push-button stop/reset red O	

Complementary

Motor Power Kw	11 kW at 380/400 V AC 50/60 Hz 11 kW at 415 V AC 50/60 Hz 11 kW at 440 V AC 50/60 Hz 15 kW at 500 V AC 50/60 Hz 15 kW at 660/690 V AC 50/60 Hz 5.5 kW at 220/230 V AC 50/60 Hz	
[Ith] Conventional Free Air Thermal Current		
[Uc] Control Circuit Voltage	240 V AC 50/60 Hz	
Cable Entry Number	2 ISO20 top 2 ISO25 top 2 ISO20 bottom 2 ISO25 bottom	
Width	101 mm	
Height	201 mm	
Depth	153.5 mm	
Net Weight	1.015 kg	

Environment

Material	Polycarbonate	
Ip Degree Of Protection	otection IP65 conforming to IEC 60529	
Ik Degree Of Protection	IK07 conforming to IEC 60529	
Standards	IEC 60947-4-1	
Ambient Air Temperature For Operation	-540 °C	
Environmental Characteristic	Standard environment	

Product Certifications UKCA

Packing Units

_	
Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	20.000 cm
Package 1 Width	16.500 cm
Package 1 Length	25.000 cm
Package 1 Weight	1.255 kg
Unit Type Of Package 2	S04
Number Of Units In Package 2	5
Package 2 Height	30.000 cm
Package 2 Width	40.000 cm
Package 2 Length	60.000 cm
Package 2 Weight	7.016 kg

Contractual warranty

Warranty 18 months



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance

Ø	Reach Free Of Svhc	
②	Toxic Heavy Metal Free	
Ø	Mercury Free	
⊘	Rohs Exemption Information	Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant EU RoHS Declaration
China Rohs Regulation	China RoHS declaration
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	End of Life Information