

Product datasheet

Specifications



LoadCentre KQ - distribution board - A type - single phase - 125A - 12 ways

Local distributor code:

396792255

SE125A12

EAN Code: 5018934960869

Main

Range	Acti9
Product Name	Load centre KQ II A
Product Or Component Type	Distribution board
Device Application	Distribution
Enclosure Type	Standard
Door Type	Overall
Provided Equipment	Enclosure Door Front cover Pan assembly Earth terminal block 25 mm ² Shielded neutral bar 25 mm ²
Colour	Grey (RAL 7035)

Complementary

Enclosure Mounting	Surface
[Ie] Rated Operational Current	125 A at 230/240 V AC
Incomer Device Options	Switch disconnecter - 2P Terminal block - 2P RCCB - 30 mA - 2P RCCB - 100 mA - 2P RCCB - 300 mA - 2P
Protection Device Options	Miniature circuit breaker (MCB) (plug-on type) as outgoer Residual current circuit breaker with overcurrent protection (RCBO) (plug-on type) as outgoer
Number Of Ways	12 ways (1P) outgoer
Cable Entry	top and bottom: knock-out side: knock-out
Height	270 mm
Width	376 mm
Depth	127 mm

Environment

Ip Degree Of Protection	IP2x B internal conforming to BS EN 60529 IP3x external conforming to BS EN 60529
-------------------------	--

Packing Units

Unit Type Of Package 1	PCE
------------------------	-----

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Number Of Units In Package 1	1
Package 1 Height	13.0 cm
Package 1 Width	31.0 cm
Package 1 Length	43.0 cm
Package 1 Weight	4.765 kg
Unit Type Of Package 2	P12
Number Of Units In Package 2	56
Package 2 Height	112.0 cm
Package 2 Width	100.0 cm
Package 2 Length	120.0 cm
Package 2 Weight	292.664 kg

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability


Green Premium™ label is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)

Well-being performance

 Rohs Exemption Information [Yes](#)

 Halogen Free Plastic Parts Product

Reach Regulation [REACH Declaration](#)

Eu Rohs Directive Pro-active compliance (Product out of EU RoHS legal scope)

China Rohs Regulation [China RoHS declaration](#)
Product out of China RoHS scope. Substance declaration for your information