Product datasheet

Specification





Modular chassis DLM type for SPACIAL WM enclosure, 168 modules, H1000xW600mm.

Local distributor code: 392869661 NSYDLM168

EAN Code: 3606480162596

Main

Range	0 11
Kange	Spacial
Accessory / Separate Part Category	Mounting accessory
Application	Multi-purpose Modular distribution application
Product Or Component Type	Chassis
Device Short Name	DLM
For Enclosure Nominal Dimensions	-
Mounting Location	Front of enclosure Step slide
Range Compatibility	Spacial Spacial S3D Spacial Spacial S3X Spacial Spacial CRN
Device Composition	1 chassis structure 2 finish cover 1 neutral/earth strip 2 x 16 mm² 5 x 6 mm² 6 front panels with 35 mm DIN rail
Quantity Per Set	Set of 1

Complementary

Material	Steel
Colour	Front panel: grey (RAL 7035)
Surface Finish	Polyester powder
Fixing Mode	By fixing element - on front and back with supports location
Adjustment	In height from 40 to 85 mm for DIN rail
Number Of Horizontal Rows	6
Total Number Of 18 Mm Modules	168
Type Of Front Plate	Plain and cut-out plates
Number Of Cut-Out	6 cut-outs
Height	953 mm
Width	555 mm
Depth	101.5 mm

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1

Package 1 Height	12.000 cm
Package 1 Width	56.500 cm
Package 1 Length	98.000 cm
Package 1 Weight	11.743 kg
Unit Type Of Package 2	PAM
Number Of Units In Package 2	15
Package 2 Height	160.000 cm
Package 2 Width	100.000 cm
Package 2 Length	120.000 cm
Package 2 Weight	189.145 kg

Contractual warranty

Warranty 18 months



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance



Mercury Free



Rohs Exemption Information

Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations