Product datasheet





(!) Discontinued

Complete miniature beacon, Harmony XVD Optimum, Ø 45 mm tower light, flashing, green, IP40, 24 V

XVDLS6B3

! Discontinued on: 1 Jul 2020

EAN Code: 3389110110746

Main

Range Of Product	Harmony XVD Optimum	
Product Or Component Type	Complete miniature beacon	
Beacon Or Indicator Bank Unit Type	Base unit direct fixing Illuminated unit	
Signalling Type	Flashing	
Mounting Diameter	45 mm	
Component Name	XVDLS	
Material	Glass reinforced polyamide: base unit Polycarbonate: illuminated unit	
Light Source	Integral flash discharge tube, green	
Bulb Type	Flash discharge tube	
[Us] Rated Supply Voltage	24 V AC/DC	

Complementary

Connections - Terminals	Screw clamp terminals, <= 1 x 1.5 mm² with cable end	
Cable Entry	1 entry tapped for Pg 7	
[Ui] Rated Insulation Voltage	250 V conforming to IEC 60947-1	
Current Consumption	< 145 mA DC < 90 mA AC	
[Uimp] Rated Impulse Withstand Voltage	4 kV conforming to IEC 60947-1	
Flash Energy	1 J	
Cad Overall Width	45 mm	
Cad Overall Height	104 mm	
Cad Overall Depth	45 mm	
Terminals Description Iso N°1	(GND)GROUND (COM-1)PW	
Net Weight	0.085 kg	

Environment

Product Certifications	CSA UL
Standards	EN/IEC 60947-5-1

Protective Treatment	TC
Ambient Air Temperature For Operation	-1050 °C
Ambient Air Temperature For Storage	-4070 °C
Electrical Shock Protection Class	Class II conforming to IEC 60536
Ip Degree Of Protection	IP40 conforming to IEC 60529

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	11 cm
Package 1 Width	5.6 cm
Package 1 Length	5.6 cm
Package 1 Weight	110 g

Contractual warranty

Warranty 18 months



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance



Mercury Free



Rohs Exemption Information

Yes

Certifications & Standards


Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
China Rohs Regulation	China RoHS declaration
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	No need of specific recycling operations

XVDLS6B3

Dimensions Drawings

Illuminated Beacon

Dimensions



Product datasheet

XVDLS6B3

Mounting and Clearance

Illuminated Beacon

Panel Cut-out for Direct Fixing

