



## pilot light Ø8 - IP40/IP65 - yellow covered LED included - 24V faston

Local distributor code: 22491192

XVLA235

EAN Code: 3389110651409

### Main

Range Of Product	Harmony XVL			
Product Or Component Type	t Or Component Type LED pilot light with integral lens cap			
Component Name	XVL			
Mounting Diameter	8 mm			
Light Source	Covered LED			
Light Block Colour	Yellow			
Protection Type	Built-in by diode Integral ballast resistor			
[Us] Rated Supply Voltage	24 V			
Ip Degree Of Protection  IP65 (with seal XVLZ911) conforming to IEC 60529  IP65 (with seal XVLZ911) conforming to NF C 20-010  IP40 conforming to IEC 60529  IP40 conforming to NF C 20-010				

## Complementary

Supply Circuit Type	DC
Connections - Terminals	Tag for Faston connectors: 2.8 x 0.5 mm Tag for soldering connectors
Current Consumption	18 mA
[Ui] Rated Insulation Voltage	50 V conforming to IEC 60947-1
Bulb Lifespan	100000 h
Nominal Voltage Limit	0.81.1 Un
Terminals Description Iso N°1	(X1-X2)PL
Height	10 mm
Width	10 mm
Depth	36 mm
Net Weight	0.003 kg

## **Environment**

Product Certifications	CSA UL
Protective Treatment	тс
Ambient Air Temperature For Operation	-2570 °C
Ambient Air Temperature For Storage	-4070 °C

Overvoltage Category	Class 3 conforming to IEC 60536	
	Class 3 conforming to NF C 20-030	

## **Packing Units**

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	1.0 cm
Package 1 Width	1.0 cm
Package 1 Length	4.2 cm
Package 1 Weight	3.0 g
Unit Type Of Package 2	BB1
Number Of Units In Package 2	10
Package 2 Height	3.0 cm
Package 2 Width	13.0 cm
Package 2 Length	14.0 cm
Package 2 Weight	34.0 g
Unit Type Of Package 3	S01
Number Of Units In Package 3	100
Package 3 Height	15.0 cm
Package 3 Width	15.0 cm
Package 3 Length	40.0 cm
Package 3 Weight	484.0 g

# **Contractual warranty**

Warranty 18 months



**Green Premium**<sup>TM</sup> **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

## Well-being performance



Mercury Free



Rohs Exemption Information

Yes

#### **Certifications & Standards**


Reach Regulation	REACh Declaration		
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)		
China Rohs Regulation	China RoHS declaration		
Environmental Disclosure	Product Environmental Profile		
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins		
Circularity Profile	No need of specific recycling operations		

#### **XVLA235**

## **Dimensions Drawings**

## **LED Pilot Light**

#### **Dimensions**



- (1) Tags for Faston connectors or soldered connections
- e panel thickness: 1 to 8 mm/0.03 to 0.31 in.


С		Ø	
mm	in.	mm	in.
34	1.34	10	0.39

## XVLA235

Mounting and Clearance

## **LED Pilot Light**

## **Panel Drilling**



Ø mi	n	G min		H min	
mm	in.	mm	in.	mm	in.
8.2	0.32	10.5	0.41	10.5	0.41