Product datasheet





84mm Rotating Mirror Green 24VAC-DC

Local distributor code: 398334242

XVR08B03

! Discontinued on: 9 Feb 2023

EAN Code: 3606480033018

! Discontinued

Main

Range Of Product	Harmony XVR	
Product Or Component Type	Prewired rotating mirror beacon	
Sound Signalling	Without	
Device Short Name	XVR	
Mounting Diameter	84 mm	
Ip Degree Of Protection	IP65 (with accessory) conforming to IEC 60529 IP23 conforming to IEC 60529	
[Us] Rated Supply Voltage	24 V AC/DC	
Light Source	High luminosity LED, green	

Complementary

Material	ABS (acrylonitrile butadiene-styrene): body part PC: globe
Cad Overall Width	84 mm
Cad Overall Depth	84 mm
Net Weight	0.3 kg
Marking	CE
Product Mounting	By 3 M4 screws
Supply Voltage Limits	1930 V DC 21.626.4 V AC
[Uimp] Rated Impulse Withstand Voltage	0.8 kV
Current Consumption	125 mA
Flashing Frequency	2.3 Hz
Clamping Connection Capacity	0.83 mm²
Awg Gauge	AWG 18
Cable Length	500 mm

Environment

Standards	IEC 61000-6-4 IEC 61000-6-2
Product Certifications	UL
Protective Treatment	TC

Life Is On Schneider 23 Apr 2024

Ambient Air Temperature For Storage	-3570 °C
Ambient Air Temperature For Operation	-1050 °C
Electrical Shock Protection Class	Class II conforming to IEC 61140

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	19 cm
Package 1 Width	9.8 cm
Package 1 Length	10 cm
Package 1 Weight	390 g
Unit Type Of Package 2	S03
Number Of Units In Package 2	6
Package 2 Height	30 cm
Package 2 Width	30 cm
Package 2 Length	40 cm
Package 2 Weight	3.053 kg
Unit Type Of Package 3	PAL
Number Of Units In Package 3	48
Package 3 Height	60 cm
Package 3 Width	80 cm
Package 3 Length	48 cm
Package 3 Weight	18.72 kg

Contractual warranty

Warranty 18 months



Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO2 products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance



Rohs Exemption Information

Certifications & Standards


Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
China Rohs Regulation	China RoHS declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End of Life Information


XVR08B03

Dimensions Drawings

Rotating Mirror Beacon

Dimensions





Product datasheet

XVR08B03

Mounting and Clearance

Rotating Mirror Beacon

Panel Cut-out

