

Product datasheet

Specifications



Acti9 - iKQ RCD - 2P - 80A - 30mA

Local distributor code:
397030903

SED80032

EAN Code: 5018934976068

Main

Range	Acti9
Product Name	iKQ
Product Or Component Type	Residual current circuit breaker
Poles Description	2P
[In] Rated Current	80 A
Network Type	AC
Earth-Leakage Sensitivity	30 mA
Rated Conditional Short-Circuit Current	6 kA

Complementary

Network Frequency	50/60 Hz
[Ue] Rated Operational Voltage	230 V AC 50/60 Hz
[Ui] Rated Insulation Voltage	500 V
[Uimp] Rated Impulse Withstand Voltage	4 kV
Control Type	Toggle
Local Signalling	Trip indicator
Mounting Mode	Fixed
Mounting Support	DIN rail
Connection Pitch	18 mm between phases
9 Mm Pitches	4
Height	81 mm
Width	36 mm
Depth	75 mm
Embedding Depth	75 mm
Net Weight	0.227 kg
Connections - Terminals	Tunnel type terminals (top or bottom) 1...25 mm² rigid Tunnel type terminals (top or bottom) 1...16 mm² flexible

Environment

Standards	BS EN 61008
Ip Degree Of Protection	IP20
Ambient Air Temperature For Operation	-5...60 °C

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	4.0 cm
Package 1 Width	8.2 cm
Package 1 Length	10.0 cm
Package 1 Weight	230.0 g

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability

Green Premium™ label is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)



Transparency RoHS/REACH

Well-being performance

✓	Mercury Free	
✓	Rohs Exemption Information	Yes
✓	Halogen Free Plastic Parts Product	

Certifications & Standards

Reach Regulation	REACH Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	No need of specific recycling operations