





Transformer, dry type, encapsulated, 0.15kVA, 1 phase, 240x480V primary, 120/240V secondary, 3A, 55C rise

150SV1A

Product availability: Stock - Normally stocked in distribution facility

Price\*: 279.00 USD

#### Main

Product Or Component Type	Dry Sealed Transformer
Primary To Secondary Voltage	240 x 480 V 120/240 V
Full Capacity Taps	0

## Complementary

Enclosure Code	3A
Phase	1 phase
Power Rating	0.15 kVA
Temperature Rise	55 °C
Height	5 in (127.00 mm)
Width	4.85 in (123.19 mm)
Depth	3.75 in (95.25 mm)
Enclosure Mounting	Wall mounted
Enclosure Material	Painted sheet steel

#### **Environment**

Enclosure Type	NEMA 3R
Insulation Temperature	221 °F (105 °C)
Product Certifications	CSA cULus III Listed

## Ordering and shipping details

Category	US10PE216277
Discount Schedule	0PE2
Gtin	785901876076
Returnability	Yes
Country Of Origin	MX

## **Packing Units**

Unit Type Of Pa	ckage 1 F	PC
-----------------	-----------	----

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Number Of Units In Package 1	1
Package 1 Height	6.42 in (16.3 cm)
Package 1 Width	6.73 in (17.1 cm)
Package 1 Length	7.40 in (18.8 cm)
Package 1 Weight	7.50 lb(US) (3.402 kg)

# **Contractual warranty**

Warranty 18 months



**Green Premium**<sup>TM</sup> **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

## Well-being performance

<b>⊘</b>	Reach Free Of Svhc
<b>⊘</b>	Toxic Heavy Metal Free
<b>⊘</b>	Mercury Free
<b>②</b>	Rohs Exemption Information Yes
<b>⊘</b>	Pvc Free

#### **Certifications & Standards**

REACh Declaration
Compliant
EU RoHS Declaration
China RoHS declaration
Pro-active China RoHS declaration (out of China RoHS legal scope)
Product Environmental Profile
No need of specific recycling operations
WARNING: This product can expose you to chemicals including: Phenyl Glycidyl Ether, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov