# **Product datasheet**





! Discontinued

LED pilot light with black bezel, Harmony XVL, Ø 8, IP40, yellow, protruding included, 5 V, faston

XVLA115

! Discontinued on: 31 Mar 2023

! End-of-service on: 15 Apr 2023

EAN Code: 3389110650983

Main

Range Of Product	Harmony XVL
Product Or Component Type	LED pilot light with black bezel
Component Name	XVL
Mounting Diameter	8 mm
Light Source	Protruding LED
Light Block Colour	Yellow
Protection Type	Built-in by diode Integral ballast resistor
[Us] Rated Supply Voltage	5 V
Ip Degree Of Protection	IP40 conforming to IEC 60529 IP40 conforming to NF C 20-010

### Complementary

•	
Supply Circuit Type	DC
Connections - Terminals	Tag for Faston connectors: 2.8 x 0.5 mm Tag for soldering connectors
Current Consumption	25 mA
[Ui] Rated Insulation Voltage	50 V conforming to IEC 60947-1
Bulb Lifespan	100000 h
Nominal Voltage Limit	0.81.1 Un
Terminals Description Iso N°1	(X1-X2)PL
Height	12 mm
Width	12 mm
Depth	34 mm
Net Weight	0.003 kg

#### **Environment**

Product Certifications	CSA UL
Protective Treatment	тс
Ambient Air Temperature For	-2570 °C

Life Is On Schneider 23 Apr 2024

Ambient Air Temperature For Storage	-4070 °C	
Overvoltage Category	Class 3 conforming to IEC 60536 Class 3 conforming to NF C 20-030	

## **Packing Units**

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	1.0 cm
Package 1 Width	1.0 cm
Package 1 Length	4.0 cm
Package 1 Weight	3.0 g
Unit Type Of Package 2	S01
Number Of Units In Package 2	100
Package 2 Height	15.0 cm
Package 2 Width	15.0 cm
Package 2 Length	40.0 cm
Package 2 Weight	596.0 g

## **Contractual warranty**

Warranty 18 months



**Green Premium**<sup>TM</sup> **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

#### Well-being performance



Mercury Free



Rohs Exemption Information

Yes


#### **Certifications & Standards**

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
China Rohs Regulation	China RoHS declaration
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	No need of specific recycling operations

#### **Dimensions Drawings**

#### **LED Pilot Light**

#### **Dimensions**



- (1) Tags for Faston connectors or soldered connections
- e panel thickness: 1 to 8 mm/0.03 to 0.31 in.


С		Ø		
mm	in.	mm	in.	
32	1.26	12	0.47	

### **XVLA115**

Mounting and Clearance

#### **LED Pilot Light**

#### **Panel Drilling**



Ø mi	n	G min		H min	
mm	in.	mm	in.	mm	in.
8.2	0.32	12.5	0.49	12.5	0.49