Product datasheet

Specification





Electronic Alarm PNP Black

Local distributor code: 398335047

XVS72BMBP

EAN Code: 3606480032905

Main

| Range Of Product | Harmony XVS |
|---------------------------|------------------|
| Product Or Component Type | Electronic alarm |
| Device Short Name | XVS |

Complementary

| Colour | Black | |
|--|---|--|
| Material | ABS (acrylonitrile butadiene-styrene): body PC (polycarbonate): terminal cover | |
| Marking | CE | |
| Overvoltage Category | Class II conforming to IEC 61140 | |
| Mounting Support | 72 mm DIN rail | |
| [Us] Rated Supply Voltage | 1224 V DC | |
| [Uimp] Rated Impulse Withstand Voltage | 0.8 kV | |
| Current Consumption | 117 mA at 12 V | |
| | 125 mA at 24 V | |
| | 158 mA at 12 V | |
| | 200 mA at 24 V | |
| Clamping Connection Capacity | <= 1 x 1.5 mm² | |
| Width | 72 mm | |
| Height | 72 mm | |
| Depth | 69.3 mm | |
| Net Weight | 0.18 kg | |

Environment

| Discrete Output Type | PNP |
|---------------------------------------|---|
| Signalling Type | 16 tones alarm |
| Standards | UL 464 IEC 61000-6-3 IEC 61000-6-2 |
| Product Certifications | UR |
| Protective Treatment | TC |
| Ambient Air Temperature For Storage | -3570 °C |
| Ambient Air Temperature For Operation | -1050 °C |
| Ip Degree Of Protection | Panel mounted: IP54 conforming to IEC 60529 |

Packing Units

| _ | |
|------------------------------|----------|
| Unit Type Of Package 1 | PCE |
| Number Of Units In Package 1 | 1 |
| Package 1 Height | 15.0 cm |
| Package 1 Width | 9.5 cm |
| Package 1 Length | 9.5 cm |
| Package 1 Weight | 266.0 g |
| Unit Type Of Package 2 | S03 |
| Number Of Units In Package 2 | 12 |
| Package 2 Height | 30.0 cm |
| Package 2 Width | 30.0 cm |
| Package 2 Length | 40.0 cm |
| Package 2 Weight | 3.905 kg |

Contractual warranty

Warranty 18 months



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance



Mercury Free



Rohs Exemption Information

Yes

Certifications & Standards

| Reach Regulation | REACh Declaration |
|--------------------------|--|
| Eu Rohs Directive | Pro-active compliance (Product out of EU RoHS legal scope) |
| China Rohs Regulation | China RoHS declaration |
| Environmental Disclosure | Product Environmental Profile |
| Circularity Profile | End of Life Information |

XVS72BMBP

Dimensions Drawings

Electronic Alarm

Dimensions

