

Product data sheet

Specifications

SQUARE D



Manual Switch - NEMA 4 - 2P - Toggle Operated - Red Indicator - 600VAC

2510KW1BH

⚠ Discontinued on: Nov 11, 2020

⚠ End-of-service on: Dec 31, 2020

⚠ Discontinued

Main

Product	Single Unit Manual Switch
Type	K

Complementary

Current Rating	30 A
Cable Entry	0.75 NPT (top and bottom)
Horsepower Rating	2 hp 115 V AC 2 hp 230 V AC 3 hp 460 V AC 3 hp 575 V AC 1 hp 90 V DC 2 hp 115 V DC 1.5 hp 230 V DC
Maximum Voltage Rating	600 V AC 230 V DC
Number Of Poles	2P
Control Unit Type	Toggle
Number Of Phases	1 phase
Pilot Light	Red indicator, 230 V
Starter Type	Non reversing
Electrical Connection	Screw clamp terminals
Wire Gauge	AWG 14...AWG 10 copper
Height	4.38 in (111.25 mm)
Width	3 in (76.20 mm)
Depth	4.56 in (115.82 mm)

Environment

Certifications	UL listed file E42243 CCN NLRV CSA LR25490 class 3211 05
Nema Enclosure Rating	NEMA 4 die cast zinc alloy standard size

Ordering and shipping details

Category	21102-2510,2511,2512 K
Discount Schedule	CP1

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Gtin	00785901784494
Returnability	No
Country Of Origin	MX

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability


Green Premium™ label is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)

Well-being performance

 Reach Free Of Svhc

 Pvc Free

Eu Rohs Directive

Not compliant

China Rohs Regulation

[China RoHS declaration](#)
Product out of China RoHS scope. Substance declaration for your information.

California Proposition 65

WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov