

Product data sheet

Specifications



Manual starter, Type M Integral Horsepower Starters, Type 1, 10hp at 380V to 575VAC, 3 phases, 3 pole, 2 speed

2512MCG1

Discontinued

Discontinued on: Aug 22, 2023

End-of-service on: Sep 15, 2023

Product availability: Non-Stock - Not normally stocked in distribution facility

Main

Product	Manual Starter
Type	M
Nema Size	M-1

Complementary

Control Unit	Push-button
Pilot Light	No indicator
Horsepower Rating	7.5 hp 200...230 V AC, 3 phase 10 hp 380...575 V AC, 3 phase
Voltage Rating	600 V AC
Number Of Poles	3P
Starter Type	2 speed
Electrical Connection	Screw clamp terminals
Overload Relay Type	Melting alloy
Number Of Thermal Units Required	3
Wire Gauge	AWG 14...AWG 8 copper
Auxiliary Contacts	Without
Height	8.63 in (219.20 mm)
Width	5 in (127.00 mm)
Depth	4.13 in (104.90 mm)

Environment

Certifications	UL listed file E42243 CCN NLRV CSA LR60905 class 3211 05
Nema Enclosure Rating	NEMA 1 painted sheet steel

Ordering and shipping details

Category	US10CP121103
Discount Schedule	0CP1

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Gtin	785901332695
Returnability	No
Country Of Origin	MX

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	6.50 in (16.51 cm)
Package 1 Width	9.50 in (24.13 cm)
Package 1 Length	10.50 in (26.67 cm)
Package 1 Weight	12.78 lb(US) (5.797 kg)

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability




Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)

Well-being performance

 Mercury Free	
 Rohs Exemption Information	Yes
 Pvc Free	
Reach Regulation	REACH Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information.
California Proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov