



Transformer, dry type, encapsulated, 2kVA, 1 phase, 208V primary, 120/240V secondary, 9A, 115C rise

2S7F

Product availability: Non-Stock - Not normally stocked in distribution facility

Price\*: 2,358.00 USD

#### Main

Product Or Component Type	Dry Sealed Transformer
Primary To Secondary Voltage	208 V 120/240 V
Full Capacity Taps	0

# Complementary

Enclosure Code	9A
Phase	1 phase
Power Rating	2 kVA
Temperature Rise	115 °C
Height	9.56 in (242.82 mm)
Width	8.68 in (220.47 mm)
Depth	6.56 in (166.62 mm)
Enclosure Mounting	Wall mounted
Enclosure Material	Painted sheet steel

#### **Environment**

Enclosure Type	NEMA 3R
Insulation Temperature	356 °F (180 °C)
Product Certifications	UL Listed cULus CSA

## Ordering and shipping details

Category	US10PE216277
Discount Schedule	0PE2
Gtin	785901015277
Returnability	No
Country Of Origin	US

## **Packing Units**

Unit <sup>-</sup>	Type Of	Package 1	PCI
Unit <sup>-</sup>	Type Of	Package 1	PC

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Number Of Units In Package 1	1
Package 1 Height	9.70 in (24.638 cm)
Package 1 Width	11.10 in (28.194 cm)
Package 1 Length	12.50 in (31.75 cm)
Package 1 Weight	49.50 lb(US) (22.453 kg)

# **Contractual warranty**

Warranty 18 months



**Green Premium**<sup>TM</sup> **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

## Well-being performance

<b>⊘</b>	Reach Free Of Svhc
<b>⊘</b>	Toxic Heavy Metal Free
<b>⊘</b>	Mercury Free
<b>⊘</b>	Rohs Exemption Information Yes
<b>⊘</b>	Pvc Free

#### **Certifications & Standards**

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant
	EU RoHS Declaration
China Rohs Regulation	China RoHS declaration
	Pro-active China RoHS declaration (out of China RoHS legal scope)
<b>Environmental Disclosure</b>	Product Environmental Profile
Circularity Profile	No need of specific recycling operations
California Proposition 65	WARNING: This product can expose you to chemicals including: Phenyl glycidyl ether, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov