





Transformer, dry type, encapsulated, 3kVA, 1 phase, 480V primary, 120/240V secondary, 10A, 115C rise

3S40FSS

Product availability: Non-Stock - Not normally stocked in distribution facility

Price*: 3,624.00 USD

Main

Product Or Component Type	Dry Sealed Transformer
Primary To Secondary Voltage	480 V 120/240 V
Full Capacity Taps	2 5 % FCBN

Complementary

Enclosure Code	10A
Phase	1 phase
Power Rating	3 kVA
Temperature Rise	115 °C
Height	10.5 in (266.70 mm)
Width	8.62 in (218.95 mm)
Depth	6.5 in (165.10 mm)
Enclosure Mounting	Wall mounted
Enclosure Material	Stainless Steel

Environment

Enclosure Type	NEMA 3R
Insulation Temperature	356 °F (180 °C)
Product Certifications	CSA cULus III Listed

Ordering and shipping details

Category	US10PE216277
Discount Schedule	0PE2
Gtin	785901766339
Returnability	No
Country Of Origin	US

Packing Units

Unit	Type Of	Package 1	PCI
Unit	Type Of	Package 1	PC

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Number Of Units In Package 1	1
Package 1 Height	11.50 in (29.21 cm)
Package 1 Width	11.00 in (27.94 cm)
Package 1 Length	16.75 in (42.545 cm)
Package 1 Weight	55.20 lb(US) (25.038 kg)

Contractual warranty

Warranty 18 months



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance

⊘	Reach Free Of Svhc
⊘	Toxic Heavy Metal Free
⊘	Mercury Free
⊘	Rohs Exemption Information Yes
⊘	Pvc Free

Certifications & Standards

REACh Declaration
Compliant
EU RoHS Declaration
China RoHS declaration
Pro-active China RoHS declaration (out of China RoHS legal scope)
Product Environmental Profile
No need of specific recycling operations
WARNING: This product can expose you to chemicals including: Phenyl glycidyl ether, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov