

Product data sheet

Specifications



Manual Starter - NEMA 12 - 3P - Size M0 - Red Indicator-NO Aux Contact - 600VAC

2510MBA2V06P11X1

⚠ Discontinued on: Oct 11, 2021

⚠ Discontinued

Main

| | |
|-----------|----------------|
| Product | Manual Starter |
| Type | M |
| Nema Size | M-0 |

Complementary

| | |
|----------------------------------|--------------------------------------------------------------|
| Control Unit | Push-button |
| Pilot Light | Red indicator, 480 V |
| Horsepower Rating | 3 hp 200...230 V AC, 3 phase 5 hp 380...575 V AC, 3 phase |
| Voltage Rating | 600 V AC |
| Number Of Poles | 3P |
| Starter Type | Non reversing |
| Electrical Connection | Pressure wire clamp |
| Overload Relay Type | Melting alloy |
| Number Of Thermal Units Required | 3 |
| Wire Gauge | AWG 14...AWG 8 copper |
| Auxiliary Contacts | 1 NO |
| Height | 10.92 in (277.37 mm) |
| Width | 5.78 in (146.81 mm) |
| Depth | 5.76 in (146.30 mm) |

Environment

| | |
|-----------------------|-------------------------------------------------------------|
| Certifications | CSA LR60905 class 3211 05 UL listed file E42243 CCN NLRV |
| Nema Enclosure Rating | NEMA 12 painted sheet steel |

Ordering and shipping details

| | |
|-------------------|--------------------------|
| Category | 21103-2510,2511,2512 M,T |
| Discount Schedule | CP1 |
| Returnability | No |
| Country Of Origin | MX |

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Packing Units

| | |
|------------------------------|-----|
| Unit Type Of Package 1 | PCE |
| Number Of Units In Package 1 | 1 |

Contractual warranty

| | |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)

California Proposition 65

WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.p65warnings.ca.gov
