

# Product data sheet

Specifications



## Reversing Manual Starter - NEMA 1 - Buttons - 3P - Size M1 - 600VAC

2511MCG1

Discontinued on: Nov 11, 2020

End-of-service on: Dec 31, 2020

Discontinued

### Main

Product	Manual Starter
Type	M
Nema Size	M-1

### Complementary

Control Unit	Push-button
Pilot Light	No indicator
Horsepower Rating	7.5 hp 200...230 V AC, 3 phase 10 hp 380...575 V AC, 3 phase
Voltage Rating	600 V AC
Number Of Poles	3P
Starter Type	Reversing
Electrical Connection	Screw clamp terminals
Overload Relay Type	Melting alloy
Number Of Thermal Units Required	3
Wire Gauge	AWG 14...AWG 8 copper
Auxiliary Contacts	Without
Height	8.63 in (219.20 mm)
Width	5 in (127.00 mm)
Depth	4.13 in (104.90 mm)

### Environment

Certifications	CSA LR60905 class 3211 05 UL listed file E42243 CCN NLRV
Nema Enclosure Rating	NEMA 1 painted sheet steel

### Ordering and shipping details

Category	21103-2510,2511,2512 M,T
Discount Schedule	CP1
Gtin	00785901332664
Returnability	No

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Country Of Origin	MX
-------------------	----

## Packing Units

Unit Type Of Package 1	PCE
------------------------	-----

Number Of Units In Package 1	1
------------------------------	---

## Contractual warranty

Warranty	18 months
----------	-----------

# Sustainability

**Green Premium™ label** is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)

Eu Rohs Directive	Not compliant
China Rohs Regulation	<a href="#">China RoHS declaration</a> Product out of China RoHS scope. Substance declaration for your information.
California Proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to <a href="#">www.P65Warnings.ca.gov</a>