

Product data sheet

Specifications



Switch, reversing drum, 5HP at 575VAC single phase, 7.5HP at 575VAC polyphase, handle operated, NEMA 4 enclosure

2601BW1

Product availability: Non-Stock - Not normally stocked in distribution facility

Price*: 776.54 USD

Main

Product	Reversing Drum Switch
Enclosure Rating	NEMA 4
Horsepower	1.5 hp 115 V AC, 1 phase 3 hp 230 V AC, 1 phase 5 hp 460 V AC, 1 phase 5 hp 575 V AC, 1 phase 5 hp 200 V AC, 3 phase 5 hp 230 V AC, 3 phase 7.5 hp 460 V AC, 3 phase 7.5 hp 575 V AC, 3 phase 2 hp 115 V DC 2 hp 230 V DC
Maximum Rated Voltage	600 V AC 250 V DC
Number Of Poles	3P

Complementary

Certifications	CSA UL Listed
Electrical Connection	Screw-clamp terminals
Type	B
Width	4.40 in (111.76 mm)
Height	6.89 in (175.01 mm)
Depth	5.50 in (139.70 mm)

Ordering and shipping details

Category	US10CP121116
Discount Schedule	0CP1
Gtin	785901784449
Returnability	Yes
Country Of Origin	MX

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Package 1 Height	4.80 in (12.192 cm)
Package 1 Width	5.00 in (12.7 cm)
Package 1 Length	8.00 in (20.32 cm)
Package 1 Weight	3.53 lb(US) (1.601 kg)

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability

Green Premium™ label is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)

Reach Regulation	REACH Declaration
Eu Rohs Directive	Not compliant
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information.
California Proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov