





Safety switch, double throw, non fusible, 200A, 600V, 3 pole, 15HP, NEMA 3R, bolt on provision

82344RB

Product availability: Stock - Normally stocked in distribution facility

Price*: 5,868.00 USD

Main

Product	Double Throw Safety Switch	
Duty Rating	General duty	
Disconnect Type	Non-fusible disconnect	
Factory Installed Neutral	None	
Number Of Poles	3	
Current Rating	200 A	
Voltage Rating	480 V AC 250 V DC	
Enclosure Rating	NEMA 3	
Motor Power Hp	15 hp at 480 V AC 50-60 Hz for 3 phase motors	

Complementary

Short-Circuit Current	10 kA H or J
Fuse Type	H or J
Mounting Type	Surface
Wire Size	AWG 6300 kcmil copper or aluminium
Tightening Torque	340 lbf.in (38.41 N.m) (AWG 6300 kcmil)
Depth	10.63 in (270.00 mm)
Width	24 in (609.60 mm)
Height	32.5 in (825.50 mm)
Net Weight	74.98 lb(US) (34.01 kg)

Environment

Certifications UL Listed

Ordering and shipping details

Category	US10DE100133	
Discount Schedule	0DE1	
Gtin	785901453819	
Returnability	Yes	
Country Of Origin	MX	

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	11.00 in (27.94 cm)
Package 1 Width	23.10 in (58.674 cm)
Package 1 Length	34.00 in (86.36 cm)
Package 1 Weight	72.90 lb(US) (33.067 kg)

Contractual warranty

Warranty 18 months



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance

⊘	Reach Free Of Svhc	
9	Toxic Heavy Metal Free	
②	Mercury Free	
⊘	Rohs Exemption Information	Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations
California Proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov