

# Product data sheet

Specifications

SQUARE D

Green Premium™



## Safety switch, double throw, non fusible, 400A, 600V, 3 pole, NEMA 1

82345

Discontinued on: Dec 23, 2020

Discontinued

### Main

Product	Double Throw Safety Switch
Duty Rating	General duty
Disconnect Type	Non-fusible disconnect
Factory Installed Neutral	None
Number Of Poles	3
Current Rating	400 A
Voltage Rating	600 V AC 600 V DC
Enclosure Rating	NEMA 1

### Complementary

Short-Circuit Current	10 kA H or J
Fuse Type	H or J
Mounting Type	Surface
Wire Size	AWG 1/0...600 kcmil copper or aluminium
Depth	10.63 in (270.00 mm)
Width	29.51 in (749.55 mm)
Height	38.5 in (977.90 mm)
Net Weight	98.99 lb(US) (44.9 kg)

### Environment

Certifications	UL Listed
----------------	-----------

### Ordering and shipping details

Category	00033-DT SWITCH,NEMA1
Discount Schedule	DE1
Gtin	785901620754
Returnability	No
Country Of Origin	US

### Packing Units

Unit Type Of Package 1	PCE
------------------------	-----

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Number Of Units In Package 1	1
Package 1 Height	11.69 in (29.7 cm)
Package 1 Width	29.49 in (74.9 cm)
Package 1 Length	43.70 in (111 cm)
Package 1 Weight	99.00 lb(US) (44.906 kg)

## Contractual warranty

Warranty	18 months
----------	-----------

Sustainability



**Green Premium™ label** is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)



Transparency   RoHS/REACH

Well-being performance

✓	Reach Free Of Svhc	
✓	Toxic Heavy Metal Free	
✓	Mercury Free	
✓	Rohs Exemption Information	Yes

Certifications & Standards

Eu Rohs Directive	Compliant <a href="#">EU RoHS Declaration</a>
China Rohs Regulation	<a href="#">China RoHS declaration</a> Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	<a href="#">Product Environmental Profile</a>