





Relay Socket, Harmony 8501R, 14 blades, double tiered screw clamp terminals, DIN rail/panel mount, 10A, 300V AC

8501NR45B

Product availability: Stock - Normally stocked in distribution facility

Price*: 32.57 USD

Main

[In] Rated Current 10 A 300 V AC

Complementary

Mounting Type	DIN rail Panel	
Electrical Connection	Double tiered screw clamp terminals	
Package Quantity	Set of 10	
Width	1.21 in (30.7 mm)	
Height	2.72 in (69 mm)	
Depth	1.00 in (25.4 mm)	

Ordering and shipping details

Category	US10CP221142	
Discount Schedule	0CP2	
Gtin	00785901006015	
Returnability	Yes	
Country Of Origin	CN	

Packing Units

_		
Unit Type Of Package 1	PCE	
Number Of Units In Package 1	1	
Package 1 Height	1.00 in (2.54 cm)	
Package 1 Width	1.20 in (3.048 cm)	
Package 1 Length	2.80 in (7.112 cm)	
Package 1 Weight	1.44 oz (40.823 g)	
Unit Type Of Package 2	CAR	
Number Of Units In Package 2	10	
Package 2 Height	2.10 in (5.334 cm)	
Package 2 Width	2.80 in (7.112 cm)	
Package 2 Length	6.30 in (16.002 cm)	

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Package 2 Weight

15.84 oz (449.056 g)

Contractual warranty

Warranty

18 months



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance

Ø	Reach Free Of Svhc	
Ø	Toxic Heavy Metal Free	
Ø	Mercury Free	
⊘	Rohs Exemption Information	Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
China Rohs Regulation	China RoHS declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations
California Proposition 65	WARNING: This product can expose you to chemicals including: Nickel compounds, which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov