





Transformer, dry type, encapsulated, 30kVA, 3 phase, 480V delta primary, 208Y/120V secondary, 16C, 115C rise

30T2FSS

Product availability: Non-Stock - Not normally stocked in distribution facility

Price*: 15,627.00 USD

Main

Product Or Component Type	Dry Sealed Transformer
Primary To Secondary Voltage	480 V delta 208Y/120 V
Full Capacity Taps	2 5 % FCBN

Complementary

Enclosure Code	16C
Phase	3 phase
Power Rating	30 kVA
Temperature Rise	115 °C
Height	22 in (558.80 mm)
Width	25 in (635.00 mm)
Depth	13.5 in (342.90 mm)
Enclosure Mounting	Wall mounted
Enclosure Material	Stainless Steel

Environment

Enclosure Type	NEMA 3R
Insulation Temperature	356 °F (180 °C)
Product Certifications	cULus CSA UL Listed

Ordering and shipping details

Category	US10PE216277
Discount Schedule	0PE2
Gtin	785901015376
Returnability	No
Country Of Origin	US

Packing Units

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Number Of Units In Package 1	1
Package 1 Height	16.40 in (41.656 cm)
Package 1 Width	25.50 in (64.77 cm)
Package 1 Length	21.30 in (54.102 cm)
Package 1 Weight	775.00 lb(US) (351.534 kg)

Contractual warranty

Warranty 18 months



Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance

⊘	Reach Free Of Svhc
⊘	Toxic Heavy Metal Free
⊘	Mercury Free
②	Rohs Exemption Information Yes
⊘	Pvc Free

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant
	EU RoHS Declaration
China Rohs Regulation	China RoHS declaration
	Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations
California Proposition 65	WARNING: This product can expose you to chemicals including: Phenyl glycidyl ether, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov