

Transformer, dry type, encapsulated, 7.5kVA, 1 phase, 600V primary, 120/240V secondary, 13B, 115C rise

7S42F

! Discontinued on: Jan 2, 2024

Product availability: Stock - Normally stocked in distribution facility

Price*: 1,459.00 USD

Main

Product Or Component Type	Dry Sealed Transformer	
Primary To Secondary Voltage	600 V 120/240 V	
Full Capacity Taps	4 2 5 % 2+ 2-	

Complementary

Enclosure Code	13B	
Phase	1 phase	
Power Rating	7.5 kVA	
Temperature Rise	115 °C	
Height	14.75 in (374.65 mm)	
Width	9.75 in (247.65 mm)	
Depth	11.75 in (298.45 mm)	
Enclosure Mounting	Wall mounted	
Enclosure Material	Painted sheet steel	

Environment

Enclosure Type	NEMA 3R	
Insulation Temperature	356 °F (180 °C)	
Product Certifications	cULus CSA UL Listed	

Ordering and shipping details

Category	38550-115 DEGREE RISE, COPPER	
Discount Schedule	SLX	
Gtin	785901390947	
Returnability	No	
Country Of Origin	US	

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Packing Units

Unit Type Of Package 1	PCE	
Number Of Units In Package 1	1	
Package 1 Height	11.22 in (28.499 cm)	
Package 1 Width	10.24 in (26.01 cm)	
Package 1 Length	13.23 in (33.604 cm)	
Package 1 Weight	135.00 lb(US) (61.235 kg)	

Contractual warranty

Warranty 18 months



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance

⊘	Reach Free Of Svhc	
⊘	Toxic Heavy Metal Free	
⊘	Mercury Free	
⊘	Rohs Exemption Information Yes	
⊘	Pvc Free	

Certifications & Standards

Reach Regulation	REACh Declaration	
Eu Rohs Directive	Compliant	
	EU RoHS Declaration	
China Rohs Regulation	China RoHS declaration	
	Pro-active China RoHS declaration (out of China RoHS legal scope)	
Environmental Disclosure	Product Environmental Profile	
Circularity Profile	No need of specific recycling operations	
California Proposition 65	WARNING: This product can expose you to chemicals including: Phenyl Glycidyl Ether, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov	