





Relay, Harmony 8501X, master, coil, screw clamp terminals, 10A resistive at 600V AC, 110/120V AC 50/60Hz, 4NO

8501XMO40V02

Product availability: Stock - Normally stocked in distribution facility

Price*: 336.00 USD

Main

Range	8501X
Relay Type	Master
Product	Relay
Current Rating	20 A AC
Contact Configuration	4 NO 4 master contact cartridges
Number Of Poles	4P
Coil Voltage	110 V AC 50 Hz 120 V AC 60 Hz
Voltage Rating	600 V AC
Mounting Type	Panel
Operating Temperature	-40160 °F (-4071 °C)
Electrical Connection	Screw clamp terminals
Certifications	CE UL Listed CSA
Operating Time	15 ms - pick-up 16 ms - drop-out
Height	3.5 in (88.90 mm)
Width	2.23 in (56.64 mm)
Depth	3.95 in (100.33 mm)

Ordering and shipping details

Category	US10CP221158
Discount Schedule	0CP2
Gtin	785901743446
Returnability	Yes
Country Of Origin	MX

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Package 1 Height	8.89 in (22.581 cm)
Package 1 Width	3.50 in (8.89 cm)
Package 1 Length	22.58 in (57.355 cm)
Package 1 Weight	33.62 oz (952.998 g)
Unit Type Of Package 2	PAL
Number Of Units In Package 2	360
Package 2 Height	40.00 in (101.6 cm)
Package 2 Width	40.00 in (101.6 cm)
Package 2 Length	48.00 in (121.92 cm)
Package 2 Weight	782.00 lb(US) (354.709 kg)

Contractual warranty

Warranty 18 months



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance



Mercury Free



Rohs Exemption Information

Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
China Rohs Regulation	China RoHS declaration
Environmental Disclosure	Product Environmental Profile
California Proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov