Specifications







NEMA Control Relay, Type X, utility, 10A resistive at 600 VAC, 12 normally open contacts, 125 VDC coil

8501XUDO1200V63

Product availability: Non-Stock - Not normally stocked in distribution facility

Price*: 629.00 USD

Main

Range	8501X
Relay Type	Utility
Product	Relay
Current Rating	10 A AC
	5 A DC
Contact Configuration	12 NO 12 standard contact cartridges
Number Of Poles	12P
Coil Voltage	125 V DC
Voltage Rating	250 V DC
Mounting Type	Panel
Operating Temperature	-40160 °F (-4071 °C)
Electrical Connection	Screw clamp terminals
Certifications	CE
	UL Listed
	CSA
Operating Time	37 ms - pick-up
	21 ms - drop-out
Height	3.56 in (90.42 mm)
Width	2.23 in (56.64 mm)
Depth	7.57 in (192.28 mm)

Ordering and shipping details

Category	US10CP221157
Discount Schedule	0CP2
Gtin	785901743347
Returnability	No
Country Of Origin	US

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1

Price is "List Price" and may be subject to a trade discount - check with your local distributor or retailer for actual price.

Package 1 Height	22.86 in (58.064 cm)
Package 1 Width	9.00 in (22.86 cm)
Package 1 Length	58.06 in (147.484 cm)
Package 1 Weight	4.05 lb(US) (1.837 kg)
Unit Type Of Package 2	PAL
Number Of Units In Package 2	252
Package 2 Height	40.00 in (101.6 cm)
Package 2 Width	40.00 in (101.6 cm)
Package 2 Length	48.00 in (121.92 cm)
Package 2 Weight	1021.92 lb(US) (463.534 kg)

Contractual warranty

Warranty

18 months

Sustainability Screen

Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

Well-being performance

Mercury Free

Rohs Exemption Information Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
China Rohs Regulation	China RoHS declaration
Environmental Disclosure	Product Environmental Profile
California Proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov