

Product data sheet

Specifications

SQUARE D



Reversing Contactor, Size 1, 3-Pole, Horizontal Open Style

8702SCO8V06

Discontinued on: Dec 12, 2019

End-of-service on: Oct 15, 2021

Discontinued

Product availability: Non-Stock - Not normally stocked in distribution facility

Main

Product Type	Contactors
Product Range	Type S
Contactors Type	Reversing

Complementary

Nema Size	1
Rated Current	27 A
Number Of Poles	3P
Mounting Orientation	Horizontal
Maximum Voltage Rating	600 V AC
Phase	3 phase
Horsepower Rating	7.5 HP 200 V AC 7.5 HP 230 V AC 10 HP 460 V AC 10 HP 575 V AC
Coil Voltage	440 V AC 50 Hz 480 V AC 60 Hz
Control Circuit Type	Common control circuit
Control Units	No control units
Other Equipment	Fuse not supplied
Terminal Type	Screw clamp terminals
Height	5.00 in (127 mm)
Width	7.13 in (181 mm)
Depth	5.31 in (135 mm)

Environment

Enclosure Type	Not rated (open device)
Certifications	CSA UL Listed

Ordering and shipping details

Category	21272 - 8702,36 SC,SD(NOT S*R,T,W)
----------	------------------------------------

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Discount Schedule	CP1
Gtin	785901724322
Returnability	No
Country Of Origin	MX

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	5.00 in (12.7 cm)
Package 1 Width	7.13 in (18.1 cm)
Package 1 Length	5.31 in (13.5 cm)
Package 1 Weight	11.00 lb(US) (4.99 kg)

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)

Eu Rohs Directive	Not compliant
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information.
California Proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds which is known to the State of California to cause Carcinogen & Reproductive harm. For more information go to www.p65warnings.ca.gov