





Contactor, Type L, multipole lighting, electrically held, 30A, 8 pole, 600V, 110/120VAC 50/60Hz coil, open style

8903LO80V02

Product availability: Stock - Normally stocked in distribution facility

Price*: 1,017.00 USD

Main

Product Or Component Type	Electrically Held Lighting Contactor
Range Of Product	8903L
Control Circuit	Separate control circuit

Complementary

Complementary		
Control Circuit Voltage	110 V AC 50 Hz 120 V AC 60 Hz	
Inrush Power In Va	180 VA 60 Hz 170 VA 50 Hz	
Hold-In Power Consumption In Va	35 VA 60 Hz 35 VA 50 Hz	
Current Rating	20 A tungsten 30 A fluorescent	
Number Of Poles	8P 8 NO	
Control Unit	No control units	
Pilot Light	No indicator	
Electrical Connection	Screw-clamp terminals	
Height	5.00 in (127 mm)	
Depth	3.11 in (79 mm)	
Width	5.63 in (143 mm)	

Environment

Enclosure Type	Not rated (open device)
Product Certifications	UL Listed CSA

Ordering and shipping details

Category	US10CP121321	
Discount Schedule	0CP1	
Gtin	785901851738	
Returnability	Yes	
Country Of Origin	US	

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Packing Units

Unit Type Of Package 1	PCE	
Number Of Units In Package 1	1	
Package 1 Height	5.71 in (14.5 cm)	
Package 1 Width	7.20 in (18.3 cm)	
Package 1 Length	7.99 in (20.3 cm)	
Package 1 Weight	3.68 lb(US) (1.67 kg)	
Unit Type Of Package 2	PAL	
Number Of Units In Package 2	Units In Package 2 126	
Package 2 Height	40.00 in (101.6 cm)	
Package 2 Width	40.00 in (101.6 cm)	
Package 2 Length	48.00 in (121.92 cm)	
Package 2 Weight	463.90 lb(US) (210.42 kg)	

Contractual warranty

Warranty 18 months



Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance

②	Reach Free Of Svhc
9	Toxic Heavy Metal Free
Ø	Mercury Free
9	Rohs Exemption Information Yes
⊘	Pvc Free
9	Halogen Free Plastic Parts Product

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations