Product data sheet

Specifications



Contactor, Type L, multipole lighting, electrically held, 30A, 3 pole, 600 V, 208 VAC 60 Hz coil, NEMA 4/4X

8903LW30V08 To be discontinued on: Sep 30, 2024

Product availability: Non-Stock - Not normally stocked in distribution facility

Price*: 959.00 USD

Main

Product Or Component Type	Electrically Held Lighting Contactor	
Range Of Product	8903L	
Control Circuit	Separate control circuit	

Complementary

Control Circuit Voltage	208 V AC 60 Hz
Inrush Power In Va	150 VA 60 Hz
Hold-In Power Consumption In Va	30 VA 60 Hz
Current Rating	20 A tungsten 30 A fluorescent
Number Of Poles	3P 3 NO
Control Unit	No control units
Pilot Light	No indicator
Electrical Connection	Screw-clamp terminals
Height	16.18 in (411 mm)
Depth	7.87 in (200 mm)
Width	8.11 in (206 mm)

Environment

Enclosure Type	NEMA 4/4X brushed stainless steel surface
Product Certifications	UL Listed CSA

Ordering and shipping details

Category	US10CP121321	
Discount Schedule	0CP1	
Returnability	No	

Packing Units

Price is "List Price" and may be subject to a trade discount - check with your local distributor or retailer for actual price.

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	16.18 in (41.1 cm)
Package 1 Width	8.11 in (20.6 cm)
Package 1 Length	7.87 in (20.0 cm)
Package 1 Weight	21.78 lb(US) (9.88 kg)

Contractual warranty

Warranty

18 months

Sustainability Screen Premium

Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

Well-being performance

Reach Free Of Svhc
Toxic Heavy Metal Free
Mercury Free
Rohs Exemption Information Yes
Pvc Free
Halogen Free Plastic Parts Product

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations