Product data sheet

Specifications







Contactor, Type L, multipole lighting, electrically held, 30A, 12 pole, 600 V, 220/240 VAC 50/60 Hz coil, NEMA 4/4X

8903LWW1200V03

Product availability: Non-Stock - Not normally stocked in distribution facility

Main

Product Or Component Type	Electrically Held Lighting Contactor	
Range Of Product	8903L	
Control Circuit	Separate control circuit	

Complementary

220 V AC 50 Hz 240 V AC 60 Hz	
180 VA 60 Hz 170 VA 50 Hz	
35 VA 60 Hz 35 VA 50 Hz	
20 A tungsten 30 A fluorescent	
12P 12 NO	
No control units	
No indicator	
Screw-clamp terminals	
13.07 in (332 mm)	
7.05 in (179 mm)	
8.50 in (216 mm)	

Environment

Enclosure Type	NEMA 4/4X glass polyester surface
Product Certifications	UL Listed CSA

Ordering and shipping details

Category	21321 - 8903 L (NOT LX)	
Discount Schedule	CP1	
Returnability	No	
Country Of Origin	MX	

Packing Units

Unit Type Of Package 1

Price is "List Price" and may be subject to a trade discount - check with your local distributor or retailer for actual price.

PCE

Number Of Units In Package 1	1
Package 1 Height	13.07 in (33.2 cm)
Package 1 Width	8.50 in (21.6 cm)
Package 1 Length	7.05 in (17.9 cm)
Package 1 Weight	65.87 lb(US) (29.88 kg)

Contractual warranty

Warranty

18 months

Sustainability Screen Premium

Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

Well-being performance

Reach Free Of Svhc
Toxic Heavy Metal Free
Mercury Free
Rohs Exemption Information Yes
Pvc Free
Halogen Free Plastic Parts Product

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations