





(!) Discontinued

8903L electrically held lighting contactor, 12 P, 12 NO, 30 A, 600 V, 277 V 60 Hz coil, NEMA 3R/12

8903LA1200V04CF

- ! Discontinued on: Dec 12, 2019
- ! End-of-service on: Oct 15, 2021

Product availability: Non-Stock - Not normally stocked in distribution facility

#### Main

Product Or Component Type	Electrically Held Lighting Contactor	
Range Of Product	8903L	
Control Circuit	Separate control circuit	

### Complementary

Control Circuit Voltage	277 V AC 60 Hz
Inrush Power In Va	180 VA 60 Hz
Hold-In Power Consumption In Va	35 VA 60 Hz
Current Rating	20 A tungsten 30 A fluorescent
Number Of Poles	12P 12 NO
Control Unit	Selector switch HAND-OFF-AUTO)
Pilot Light	No indicator
Control Circuit Fusing	1 fuse
Electrical Connection	Screw-clamp terminals
Height	13.50 in (343 mm)
Depth	7.76 in (197 mm)
Width	11.89 in (302 mm)

### **Environment**

Enclosure Type	NEMA 12 painted sheet steel surface
Product Certifications	UL Listed

### Ordering and shipping details

Category	21321 - 8903 L (NOT LX)	
Discount Schedule	CP1	
Returnability	No	
Country Of Origin	MX	

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

# **Packing Units**

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	13.50 in (34.3 cm)
Package 1 Width	11.89 in (30.2 cm)
Package 1 Length	7.76 in (19.7 cm)
Package 1 Weight	22.22 lb(US) (10.08 kg)

## **Contractual warranty**

Warranty 18 months

Apr 24, 2024



**Green Premium<sup>TM</sup> label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

### Well-being performance

<b>⊘</b>	Reach Free Of Svhc
<b>⊘</b>	Mercury Free
<b>②</b>	Rohs Exemption Information Yes
<b>②</b>	Pvc Free
<b>⊘</b>	Halogen Free Plastic Parts Product

### **Certifications & Standards**

Eu Rohs Directive	Compliant
	EU RoHS Declaration
China Rohs Regulation	China RoHS declaration  Product out of China RoHS scope. Substance declaration for your information.
Environmental Disclosure	Product Environmental Profile
California Proposition 65	WARNING: Cancer and Reproductive Harm - www.P65Warnings.ca.gov