





Contactor, Type L, multipole lighting, mechanically held, 30A, 3 pole, 600 V, 277 VAC 60 Hz coil, open style

8903LXO30V04

Product availability: Non-Stock - Not normally stocked in distribution facility

Price*: 624.00 USD

Main

Product Or Component Type	Mechanically Held Lighting Contactor
Range Of Product	8903LX
Control Circuit	Separate control circuit

Complementary

Control Voltage	277 V AC 60 Hz	
Inrush Power In Va	150 VA 60 Hz 170 VA 50/60 Hz	
Current Rating	20 A tungsten 30 A fluorescent	
Number Of Poles	3P 3 NO	
Control Unit	No control units	
Pilot Light	No indicator	
Other Options	None	
Electrical Connection	Screw-clamp terminals	
Height	8.82 in (224 mm)	
Depth	3.27 in (83 mm)	
Width	2.87 in (73 mm)	

Environment

Enclosure Type	Not rated (open device)
Product Certifications	UL Listed CSA

Ordering and shipping details

Category	US10CP121322	
Discount Schedule	0CP1	
Gtin	785901057291	
Returnability	No	
Country Of Origin	MX	

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	4.00 in (10.16 cm)
Package 1 Width	7.50 in (19.05 cm)
Package 1 Length	10.50 in (26.67 cm)
Package 1 Weight	8.70 lb(US) (3.946 kg)

Contractual warranty

Warranty 18 months



Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance

⊘	Reach Free Of Svhc
⊘	Toxic Heavy Metal Free
②	Mercury Free
9	Rohs Exemption Information Yes
⊘	Pvc Free
9	Halogen Free Plastic Parts Product

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations
California Proposition 65	WARNING: Cancer and Reproductive Harm - www.P65Warnings.ca.gov