# **Product data sheet**

Specifications



Green



# Contactor, Type L, multipole lighting, mechanically held, 30A, 3 pole, 600 V, 440/480 VAC 50/60 Hz coil, NEMA 4/4X

8903LXWW30V06

Product availability: Non-Stock - Not normally stocked in distribution facility

Main	
Product Or Component Type	Mechanically Held Lighting Contactor
Range Of Product	8903LX
Control Circuit	Separate control circuit
Complementary	
Control Voltage	440 V AC 50 Hz 480 V AC 60 Hz
Inrush Power In Va	150 VA 60 Hz 150 VA 50 Hz 170 VA 50/60 Hz
Current Rating	20 A tungsten 30 A fluorescent
Number Of Poles	3P 3 NO
Control Unit	No control units
Pilot Light	No indicator
Other Options	None
Electrical Connection	Screw-clamp terminals
Height	13.90 in (353 mm)
Depth	7.05 in (179 mm)
Width	8.50 in (216 mm)

#### Environment

Enclosure Type	NEMA 4/4X glass polyester surface
Product Certifications	UL Listed CSA

### Ordering and shipping details

Category	21322 - 8903 LX (NOT L)
Discount Schedule	CP1
Returnability	No
Country Of Origin	MX

#### **Packing Units**

Unit Type Of Package 1

Price is "List Price" and may be subject to a trade discount - check with your local distributor or retailer for actual price.

PCE

Number Of Units In Package 1	1
Package 1 Height	13.90 in (35.3 cm)
Package 1 Width	8.50 in (21.6 cm)
Package 1 Length	7.05 in (17.9 cm)
Package 1 Weight	83.51 lb(US) (37.88 kg)

## **Contractual warranty**

Warranty

18 months

## Sustainability Screen Premium

**Green Premium<sup>TM</sup> label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

### Well-being performance

Reach Free Of Svhc
Toxic Heavy Metal Free
Mercury Free
Rohs Exemption Information Yes
Pvc Free
Halogen Free Plastic Parts Product

#### **Certifications & Standards**

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations
California Proposition 65	WARNING: Cancer and Reproductive Harm - www.P65Warnings.ca.gov