





Contactor, Type L, multipole lighting, electrically held, 30A, 8 pole, 600 V, 110/120 VAC 50/60 Hz coil, NEMA 1 flush

8903LF80V02C

Product availability: Non-Stock - Not normally stocked in distribution facility

Main

Product Or Component Type	Electrically Held Lighting Contactor
Range Of Product	8903L
Control Circuit	Sanarate control circuit

Complementary

Complementary		
Control Circuit Voltage	110 V AC 50 Hz	
	120 V AC 60 Hz	
Inrush Power In Va	180 VA 60 Hz	
	170 VA 50 Hz	
Hold-In Power Consumption In Va	35 VA 60 Hz	
	35 VA 50 Hz	
Current Rating	20 A tungsten	
	30 A fluorescent	
Number Of Poles	8P 8 NO	
Control Unit	Selector switch HAND-OFF-AUTO)	
Pilot Light	No indicator	
Electrical Connection	Screw-clamp terminals	
Height	20.08 in (510 mm)	
Depth	7.13 in (181 mm)	
Width	17.52 in (445 mm)	

Environment

Enclosure Type	NEMA 1 painted sheet steel flush
Product Certifications	UL Listed

Ordering and shipping details

Category	21321 - 8903 L (NOT LX)
Discount Schedule	CP1
Returnability	No
Country Of Origin	MX

Packing Units

Unit Type Of Package 1	PCE	

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Number Of Units In Package 1 1

Package 1 Weight 39.64 lb(US) (17.98 kg)

Contractual warranty

Warranty 18 months



Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance

⊘	Reach Free Of Svhc
⊘	Toxic Heavy Metal Free
②	Mercury Free
9	Rohs Exemption Information Yes
⊘	Pvc Free
9	Halogen Free Plastic Parts Product

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations
California Proposition 65	WARNING: Cancer and Reproductive Harm - www.P65Warnings.ca.gov